

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P#

Luminaire Tested: **LD4C08D010 EX4C089027 4LBSQH**

Issue Date: 2/9/2022



**Test Information**


Test Method: LM-79-08  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/9/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C08D010 EX4C089027 4LBSQH  
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS AND 4LBSQ TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 673.0 lumens  
Efficiency: N/A  
Efficacy: 68.0 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P#  
CATALOG NUMBER: LD4C08D010 EX4C089027 4LBSQH

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD4C08D010 EX4C089027 4LBSQH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73	73	73	73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67	67	67	67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62	62	62	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58	58	58	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54	54	54	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50	50	50	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47	47	47	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	64387
5°	63451
10°	60805
15°	57428
20°	53610
25°	48665
30°	40633
35°	29436
40°	18428
45°	10534
50°	5494
55°	3078
60°	1968
65°	1164
70°	846
75°	373
80°	556
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD4C08D010 EX4C089027 4LBSQH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.4	9.1
10°-20°	161.1	23.9
20°-30°	207.0	30.8
30°-40°	155.8	23.1
40°-50°	62.6	9.3
50°-60°	17.8	2.6
60°-70°	5.6	0.8
70°-80°	1.6	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	429.5	63.8
0°-40°	585.3	87.0
0°-60°	665.7	98.9
0°-90°	673.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	673.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	667	
5°	655	61
15°	575	161
25°	457	207
35°	250	156
45°	77	63
55°	18	18
65°	5	6
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD4C08D010 EX4C089027 4LBSQH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	667.3
2.5°	663.3
5°	655.1
7.5°	639.9
10°	620.6
12.5°	597.3
15°	574.9
17.5°	549.5
20°	522.1
22.5°	492.6
25°	457.1
27.5°	414.4
30°	364.7
32.5°	308.8
35°	249.9
37.5°	195.0
40°	146.3
42.5°	107.7
45°	77.2
47.5°	52.8
50°	36.6
52.5°	25.4
55°	18.3
57.5°	13.2
60°	10.2
62.5°	7.1
65°	5.1
67.5°	4.1
70°	3.0
72.5°	2.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)