

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563893

Luminaire Tested: **LD4C08D010 EX4C08D2W 4LCSQWLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P563893
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-13)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C08D010 EX4C08D2W 4LCSQWLI
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LCSQW TRIM WITH LI FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 686.6 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.9
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563893

CATALOG NUMBER: LD4C08D010 EX4C08D2W 4LCSQWLI

Luminous Intensity Polar Plot





TEST NUMBER: P563893

CATALOG NUMBER: LD4C08D010 EX4C08D2W 4LCSQWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81																			
4	98	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71																			
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66																			
7	84	75	69	65	82	74	68	64	73	68	64	71	67	64	70	66	63	62																			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58																			
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55																			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	74007	74007	74007
5°	74077	73738	73738
10°	73101	72670	72454
15°	70734	70394	69925
20°	65511	66938	64792
25°	52678	60216	51986
30°	34773	47218	33948
35°	21732	28352	21344
40°	14183	13137	13629
45°	6823	5254	6441
50°	1726	2087	1621
55°	942	858	925
60°	656	540	618
65°	434	388	434
70°	339	282	339
75°	261	261	261
80°	167	278	278
85°	221	332	332



TEST NUMBER: P563893

CATALOG NUMBER: LD4C08D010 EX4C08D2W 4LCSQWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.1	10.5
10°-20°	197.0	28.7
20°-30°	234.7	34.2
30°-40°	132.9	19.4
40°-50°	41.1	6.0
50°-60°	5.7	0.8
60°-70°	1.9	0.3
70°-80°	0.8	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	503.8	73.4
0°-40°	636.8	92.7
0°-60°	683.6	99.6
0°-90°	686.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	686.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	765	763	761	761	761	72
15°	708	707	705	702	700	197
25°	495	524	566	524	488	221
35°	184	201	241	202	181	120
45°	50	58	38	57	47	41
55°	6	6	5	6	6	6
65°	2	2	2	2	2	2
75°	1	1	1	1	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P563893

CATALOG NUMBER: LD4C08D010 EX4C08D2W 4LCSQWLI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	767.0	767.0	767.0	767.0	767.0
2.5°	767.2	765.8	765.5	765.2	765.8
5°	764.8	763.1	761.3	760.8	761.3
7.5°	758.3	756.6	753.5	752.8	753.4
10°	746.1	744.6	741.7	740.2	739.5
12.5°	730.1	727.5	724.9	723.1	721.3
15°	708.1	706.9	704.7	702.0	700.0
17.5°	677.7	679.4	680.6	675.0	669.8
20°	638.0	644.5	651.9	640.4	631.0
22.5°	576.1	594.9	613.7	592.0	570.9
25°	494.8	523.7	565.6	524.5	488.3
27.5°	399.8	436.4	502.5	436.6	394.5
30°	312.1	349.7	423.8	344.8	304.7
32.5°	239.7	267.8	331.1	263.6	234.5
35°	184.5	201.2	240.7	201.7	181.2
37.5°	143.4	151.9	161.9	148.9	139.2
40°	112.6	112.9	104.3	111.2	108.2
42.5°	83.5	83.2	64.1	81.1	81.6
45°	50.0	58.3	38.5	56.8	47.2
47.5°	23.8	33.0	23.1	31.2	22.1
50°	11.5	15.9	13.9	14.7	10.8
52.5°	7.7	8.1	7.9	7.7	7.4
55°	5.6	5.6	5.1	5.5	5.5
57.5°	4.3	4.3	3.7	4.1	4.1
60°	3.4	3.2	2.8	3.2	3.2
62.5°	2.4	2.4	2.1	2.4	2.4
65°	1.9	1.9	1.7	1.9	1.9
67.5°	1.6	1.6	1.2	1.6	1.4
70°	1.2	1.2	1.0	1.2	1.2
72.5°	0.9	0.9	0.9	0.9	0.9
75°	0.7	0.7	0.7	0.7	0.7
77.5°	0.5	0.5	0.5	0.5	0.5
80°	0.3	0.3	0.5	0.5	0.5
82.5°	0.3	0.3	0.3	0.3	0.3
85°	0.2	0.3	0.3	0.3	0.3
87.5°	0.2	0.2	0.3	0.3	0.3
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)