

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P#

Luminaire Tested: **LD4C10D010 EX4C109035 4LCSQWH**

Issue Date: 2/18/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-14)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10D010 EX4C109035 4LCSQWH
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LCSQW TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 676.0 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.94
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P#
CATALOG NUMBER: LD4C10D010 EX4C109035 4LCSQWH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD4C10D010 EX4C109035 4LCSQWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92															
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84															
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77				77															
4	95	87	80	76	93	85	80	75	83	78	74	81	77	74	79	76	73	71				71															
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	66				66															
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61				61															
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	65	61	58	56				56															
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52				52															
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49				49															
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46															

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	61627	61627	61627
5°	61059	61020	61040
10°	59502	59267	59502
15°	58068	57019	58128
20°	55058	54852	55160
25°	45162	51528	45396
30°	32199	42572	32244
35°	23228	28211	23299
40°	18616	16387	18616
45°	14205	9566	14096
50°	9367	6109	9337
55°	6308	4105	6241
60°	4246	2798	4284
65°	2900	1986	2854
70°	1918	1411	1918
75°	1268	1044	1268
80°	889	778	889
85°	664	664	664



TEST NUMBER: P#

CATALOG NUMBER: LD4C10D010 EX4C109035 4LCSQWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.4	8.8
10°-20°	161.9	23.9
20°-30°	202.4	29.9
30°-40°	136.2	20.1
40°-50°	71.9	10.6
50°-60°	29.2	4.3
60°-70°	10.8	1.6
70°-80°	3.5	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	423.7	62.7
0°-40°	559.8	82.8
0°-60°	660.9	97.8
0°-90°	676.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	676.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	639	639	639	639	639	
5°	630	630	630	630	630	59
15°	581	576	571	576	582	163
25°	424	448	484	449	426	191
35°	197	207	240	208	198	127
45°	104	99	70	98	103	80
55°	38	31	24	31	37	35
65°	13	10	9	10	12	13
75°	3	3	3	3	3	4
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P#

CATALOG NUMBER: LD4C10D010 EX4C109035 4LCSQWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	638.7	638.7	638.7	638.7	638.7
2.5°	637.1	636.7	636.5	636.5	636.7
5°	630.4	629.8	630.0	630.0	630.2
7.5°	619.8	619.6	619.0	619.8	619.8
10°	607.3	606.3	604.9	606.5	607.3
12.5°	594.4	591.4	588.9	591.4	594.4
15°	581.3	576.5	570.8	576.3	581.9
17.5°	564.2	559.3	553.1	560.3	565.8
20°	536.2	536.6	534.2	536.2	537.2
22.5°	491.3	500.3	513.0	500.5	489.8
25°	424.2	448.0	484.0	448.8	426.4
27.5°	352.3	382.5	441.5	384.3	354.5
30°	289.0	315.8	382.1	317.6	289.4
32.5°	234.0	254.0	310.6	256.4	236.7
35°	197.2	207.1	239.5	207.5	197.8
37.5°	169.0	169.0	177.9	169.8	168.2
40°	147.8	141.4	130.1	141.2	147.8
42.5°	128.1	118.4	94.5	118.0	128.5
45°	104.1	98.9	70.1	98.5	103.3
47.5°	80.0	76.3	52.8	75.9	80.6
50°	62.4	56.8	40.7	56.4	62.2
52.5°	47.9	41.9	31.4	41.9	47.5
55°	37.5	31.4	24.4	31.4	37.1
57.5°	28.8	24.0	18.5	23.6	28.6
60°	22.0	17.9	14.5	17.9	22.2
62.5°	16.7	13.7	11.1	13.5	16.5
65°	12.7	10.3	8.7	10.3	12.5
67.5°	9.3	7.7	6.6	7.7	9.5
70°	6.8	5.8	5.0	5.6	6.8
72.5°	5.0	4.2	3.8	4.2	5.0
75°	3.4	3.0	2.8	3.0	3.4
77.5°	2.4	2.2	2.0	2.2	2.4
80°	1.6	1.4	1.4	1.6	1.6
82.5°	1.0	1.0	1.0	1.0	1.0
85°	0.6	0.6	0.6	0.6	0.6
87.5°	0.4	0.4	0.4	0.4	0.4
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)