

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P#

Luminaire Tested: **LD4C35D010 EX4C359040 4LBSQH**

Issue Date: 2/9/2022



**Test Information**


Test Method: LM-79-08  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/9/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C35D010 EX4C359040 4LBSQH  
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS  
AND 4LBSQ TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2804.0 lumens  
Efficiency: N/A  
Efficacy: 69.4 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 40.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P#  
CATALOG NUMBER: LD4C35D010 EX4C359040 4LBSQH

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD4C35D010 EX4C359040 4LBSQH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73	73	73	73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67	67	67	67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62	62	62	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58	58	58	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54	54	54	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50	50	50	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47	47	47	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	268268
5°	264372
10°	253330
15°	239273
20°	223342
25°	202749
30°	169274
35°	122632
40°	76771
45°	43884
50°	22877
55°	12819
60°	8163
65°	4840
70°	3583
75°	1566
80°	2334
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD4C35D010 EX4C359040 4LBSQH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	255.8	9.1
10°-20°	671.2	23.9
20°-30°	862.6	30.8
30°-40°	649.0	23.1
40°-50°	260.6	9.3
50°-60°	74.1	2.6
60°-70°	23.4	0.8
70°-80°	6.7	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1789.6	63.8
0°-40°	2438.5	87.0
0°-60°	2773.3	98.9
0°-90°	2804.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2804.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2780	
5°	2730	256
15°	2395	671
25°	1904	863
35°	1041	649
45°	322	261
55°	76	74
65°	21	23
75°	4	7
85°	0	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD4C35D010 EX4C359040 4LBSQH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2780.3
2.5°	2763.4
5°	2729.5
7.5°	2666.0
10°	2585.6
12.5°	2488.4
15°	2395.3
17.5°	2289.4
20°	2175.1
22.5°	2052.5
25°	1904.4
27.5°	1726.6
30°	1519.3
32.5°	1286.4
35°	1041.1
37.5°	812.5
40°	609.5
42.5°	448.6
45°	321.6
47.5°	220.1
50°	152.4
52.5°	105.8
55°	76.2
57.5°	55.0
60°	42.3
62.5°	29.6
65°	21.2
67.5°	16.9
70°	12.7
72.5°	8.5
75°	4.2
77.5°	4.2
80°	4.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)