

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P#

Luminaire Tested: **LD4C40D010 EX4C409030 4LBSQH**

Issue Date: 2/9/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C40D010 EX4C409030 4LBSQH
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBSQ TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3205.0 lumens
Efficiency: N/A
Efficacy: 68.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P#
CATALOG NUMBER: LD4C40D010 EX4C409030 4LBSQH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD4C40D010 EX4C409030 4LBSQH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	306642
5°	302186
10°	289562
15°	273486
20°	255286
25°	231740
30°	193485
35°	140172
40°	87742
45°	50161
50°	26149
55°	14652
60°	9340
65°	5525
70°	4091
75°	1789
80°	2667
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD4C40D010 EX4C409030 4LBSQH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.4	9.1
10°-20°	767.2	23.9
20°-30°	985.9	30.8
30°-40°	741.8	23.1
40°-50°	297.9	9.3
50°-60°	84.7	2.6
60°-70°	26.8	0.8
70°-80°	7.6	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2045.5	63.8
0°-40°	2787.3	87.0
0°-60°	3169.9	98.9
0°-90°	3205.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3205.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3178	
5°	3120	292
15°	2738	767
25°	2177	986
35°	1190	742
45°	368	298
55°	87	85
65°	24	27
75°	5	8
85°	0	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD4C40D010 EX4C409030 4LBSQH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3178.0
2.5°	3158.6
5°	3119.9
7.5°	3047.3
10°	2955.4
12.5°	2844.3
15°	2737.8
17.5°	2616.8
20°	2486.2
22.5°	2346.1
25°	2176.7
27.5°	1973.5
30°	1736.6
32.5°	1470.4
35°	1190.0
37.5°	928.7
40°	696.6
42.5°	512.7
45°	367.6
47.5°	251.6
50°	174.2
52.5°	121.0
55°	87.1
57.5°	62.9
60°	48.4
62.5°	33.9
65°	24.2
67.5°	19.4
70°	14.5
72.5°	9.7
75°	4.8
77.5°	4.8
80°	4.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)