

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563852

Luminaire Tested: **LD4C05D010 EX4C05D2W 4LBSQH**

Issue Date: 2/9/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P563852  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/9/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C05D010 EX4C05D2W 4LBSQH  
Description: 4 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LBSQ TRIM WITH H FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 529.9 lumens  
Efficiency: N/A  
Efficacy: 73.6 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P563852

CATALOG NUMBER: LD4C05D010 EX4C05D2W 4LBSQH

### Luminous Intensity Polar Plot





TEST NUMBER: P563852

CATALOG NUMBER: LD4C05D010 EX4C05D2W 4LBSQH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73	73	73	73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67	67	67	67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62	62	62	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58	58	58	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54	54	54	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50	50	50	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47	47	47	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	50705
5°	49969
10°	47882
15°	45231
20°	42223
25°	38316
30°	31999
35°	23170
40°	14498
45°	8283
50°	4323
55°	2422
60°	1544
65°	913
70°	677
75°	298
80°	445
85°	0



TEST NUMBER: P563852

CATALOG NUMBER: LD4C05D010 EX4C05D2W 4LBSQH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.4	9.1
10°-20°	126.9	23.9
20°-30°	163.0	30.8
30°-40°	122.6	23.1
40°-50°	49.2	9.3
50°-60°	14.0	2.6
60°-70°	4.4	0.8
70°-80°	1.3	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	338.3	63.8
0°-40°	460.9	87.0
0°-60°	524.1	98.9
0°-90°	529.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	529.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	526	
5°	516	48
15°	453	127
25°	360	163
35°	197	123
45°	61	49
55°	14	14
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P563852

CATALOG NUMBER: LD4C05D010 EX4C05D2W 4LBSQH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	525.5
2.5°	522.3
5°	515.9
7.5°	503.9
10°	488.7
12.5°	470.4
15°	452.8
17.5°	432.7
20°	411.2
22.5°	388.0
25°	359.9
27.5°	326.3
30°	287.2
32.5°	243.1
35°	196.7
37.5°	153.6
40°	115.1
42.5°	84.7
45°	60.7
47.5°	41.6
50°	28.8
52.5°	20.0
55°	14.4
57.5°	10.4
60°	8.0
62.5°	5.6
65°	4.0
67.5°	3.2
70°	2.4
72.5°	1.6
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)