

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840281

Luminaire Tested: **LDS4C05D010 EU4059030 4LBPSSQMMS**

Issue Date: 8/24/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P840281  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C05D010 EU4059030 4LBPSSQMMS  
Description: 4 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LBPSSQ TRIM WITH MMS FINISH  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 525.1 lumens  
Efficiency: N/A  
Efficacy: 72.9 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P840281

CATALOG NUMBER: LDS4C05D010 EU4059030 4LBPSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P840281

CATALOG NUMBER: LDS4C05D010 EU4059030 4LBPSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	26602
5°	26510
10°	26219
15°	25762
20°	25188
25°	24519
30°	23743
35°	22828
40°	21677
45°	19704
50°	16272
55°	11977
60°	8124
65°	4772
70°	1890
75°	410
80°	556
85°	996



TEST NUMBER: P840281

CATALOG NUMBER: LDS4C05D010 EU4059030 4LBPSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	25.9	4.9
10°-20°	72.6	13.8
20°-30°	106.0	20.2
30°-40°	120.9	23.0
40°-50°	109.9	20.9
50°-60°	64.8	12.3
60°-70°	21.8	4.1
70°-80°	2.3	0.4
80°-90°	0.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	204.5	38.9
0°-40°	325.4	62.0
0°-60°	500.2	95.3
0°-90°	525.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	525.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	276	
5°	274	26
15°	258	73
25°	230	106
35°	194	121
45°	144	110
55°	71	65
65°	21	22
75°	1	2
85°	1	1
90°	0	



TEST NUMBER: P840281

CATALOG NUMBER: LDS4C05D010 EU4059030 4LBPSSQMMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	275.7
2.5°	275.2
5°	273.7
7.5°	271.1
10°	267.6
12.5°	263.0
15°	257.9
17.5°	252.0
20°	245.3
22.5°	238.1
25°	230.3
27.5°	221.8
30°	213.1
32.5°	203.6
35°	193.8
37.5°	183.2
40°	172.1
42.5°	159.2
45°	144.4
47.5°	127.4
50°	108.4
52.5°	89.4
55°	71.2
57.5°	55.8
60°	42.1
62.5°	30.5
65°	20.9
67.5°	12.8
70°	6.7
72.5°	2.6
75°	1.1
77.5°	1.1
80°	1.0
82.5°	0.9
85°	0.9
87.5°	0.7
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)