

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840307

Luminaire Tested: **LDS4C100D010 EU41009050 4LPSSQMMS**

Issue Date: 8/24/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P840307  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C100D010 EU41009050 4LBPSSQMMS  
Description: 4 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 4LBPSSQ TRIM WITH MMS FINISH  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8430.0 lumens  
Efficiency: N/A  
Efficacy: 73.7 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 114.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P840307

CATALOG NUMBER: LDS4C100D010 EU41009050 4LBPSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P840307

CATALOG NUMBER: LDS4C100D010 EU41009050 4LBPSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90																											
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79																											
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70																											
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62																											
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55																											
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49																											
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44																											
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40																											
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36																											
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	427098
5°	425640
10°	420970
15°	413725
20°	404452
25°	393639
30°	381243
35°	366554
40°	348070
45°	316469
50°	261267
55°	192380
60°	130569
65°	76462
70°	30214
75°	6785
80°	8835
85°	15167



TEST NUMBER: P840307

CATALOG NUMBER: LDS4C100D010 EU41009050 4LBPSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	416.4	4.9
10°-20°	1166.2	13.8
20°-30°	1701.1	20.2
30°-40°	1941.7	23.0
40°-50°	1765.2	20.9
50°-60°	1041.1	12.3
60°-70°	349.2	4.1
70°-80°	36.4	0.4
80°-90°	12.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3283.7	39.0
0°-40°	5225.3	62.0
0°-60°	8031.6	95.3
0°-90°	8430.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8430.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4426	
5°	4394	416
15°	4142	1166
25°	3697	1701
35°	3112	1942
45°	2319	1765
55°	1144	1041
65°	335	349
75°	18	36
85°	14	13
90°	0	



TEST NUMBER: P840307

CATALOG NUMBER: LDS4C100D010 EU41009050 4LBPSSQMMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4426.4
2.5°	4419.6
5°	4394.5
7.5°	4353.5
10°	4296.6
12.5°	4223.7
15°	4141.7
17.5°	4046.0
20°	3938.9
22.5°	3822.7
25°	3697.4
27.5°	3560.7
30°	3421.8
32.5°	3269.1
35°	3111.9
37.5°	2941.1
40°	2763.4
42.5°	2556.1
45°	2319.2
47.5°	2045.8
50°	1740.5
52.5°	1435.2
55°	1143.6
57.5°	895.3
60°	676.6
62.5°	489.8
65°	334.9
67.5°	205.0
70°	107.1
72.5°	41.0
75°	18.2
77.5°	18.2
80°	15.9
82.5°	13.7
85°	13.7
87.5°	11.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)