

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840317

Luminaire Tested: **LDS4C10D010 EU4109050 4LBPSSQMMS**

Issue Date: 8/24/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P840317
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C10D010 EU4109050 4LBPSSQMMS
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBPSSQ TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 838.0 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P840317

CATALOG NUMBER: LDS4C10D010 EU4109050 4LBPSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P840317

CATALOG NUMBER: LDS4C10D010 EU4109050 4LBPSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42455
5°	42307
10°	41846
15°	41126
20°	40210
25°	39136
30°	37893
35°	36433
40°	34600
45°	31453
50°	25969
55°	19127
60°	12987
65°	7603
70°	2990
75°	671
80°	889
85°	1550



TEST NUMBER: P840317

CATALOG NUMBER: LDS4C10D010 EU4109050 4LBPSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.4	4.9
10°-20°	115.9	13.8
20°-30°	169.1	20.2
30°-40°	193.0	23.0
40°-50°	175.5	20.9
50°-60°	103.5	12.4
60°-70°	34.7	4.1
70°-80°	3.6	0.4
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	326.4	39.0
0°-40°	519.4	62.0
0°-60°	798.4	95.3
0°-90°	838.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	838.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	440	
5°	437	41
15°	412	116
25°	368	169
35°	309	193
45°	230	175
55°	114	104
65°	33	35
75°	2	4
85°	1	1
90°	0	



TEST NUMBER: P840317

CATALOG NUMBER: LDS4C10D010 EU4109050 4LBPSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	440.0
2.5°	439.3
5°	436.8
7.5°	432.8
10°	427.1
12.5°	419.9
15°	411.7
17.5°	402.2
20°	391.6
22.5°	380.0
25°	367.6
27.5°	354.0
30°	340.1
32.5°	325.0
35°	309.3
37.5°	292.4
40°	274.7
42.5°	254.1
45°	230.5
47.5°	203.4
50°	173.0
52.5°	142.7
55°	113.7
57.5°	89.0
60°	67.3
62.5°	48.7
65°	33.3
67.5°	20.4
70°	10.6
72.5°	4.1
75°	1.8
77.5°	1.8
80°	1.6
82.5°	1.4
85°	1.4
87.5°	1.1
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)