

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840349

Luminaire Tested: **LDS4C30D010 EU4309027 4LBPSSQMMS**

Issue Date: 8/24/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P840349
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C30D010 EU4309027 4LBPSSQMMS
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBPSSQ TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2268.0 lumens
Efficiency: N/A
Efficacy: 71.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P840349

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBPSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P840349

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBPSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114909
5°	114515
10°	113252
15°	111310
20°	108811
25°	105910
30°	102569
35°	98615
40°	93649
45°	85135
50°	70297
55°	51762
60°	35122
65°	20571
70°	8125
75°	1827
80°	2389
85°	4096



TEST NUMBER: P840349

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBPSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.0	4.9
10°-20°	313.8	13.8
20°-30°	457.7	20.2
30°-40°	522.4	23.0
40°-50°	474.9	20.9
50°-60°	280.1	12.3
60°-70°	93.9	4.1
70°-80°	9.8	0.4
80°-90°	3.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	883.4	39.0
0°-40°	1405.8	62.0
0°-60°	2160.8	95.3
0°-90°	2268.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2268.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1191	
5°	1182	112
15°	1114	314
25°	995	458
35°	837	522
45°	624	475
55°	308	280
65°	90	94
75°	5	10
85°	4	3
90°	0	



TEST NUMBER: P840349

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBPSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1190.9
2.5°	1189.0
5°	1182.3
7.5°	1171.3
10°	1155.9
12.5°	1136.3
15°	1114.3
17.5°	1088.5
20°	1059.7
22.5°	1028.5
25°	994.8
27.5°	958.0
30°	920.6
32.5°	879.5
35°	837.2
37.5°	791.3
40°	743.5
42.5°	687.7
45°	623.9
47.5°	550.4
50°	468.3
52.5°	386.1
55°	307.7
57.5°	240.9
60°	182.0
62.5°	131.8
65°	90.1
67.5°	55.2
70°	28.8
72.5°	11.0
75°	4.9
77.5°	4.9
80°	4.3
82.5°	3.7
85°	3.7
87.5°	3.1
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)