

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840368

Luminaire Tested: **LDS4C40D010 EU4409027 4LBPSSQMB**

Issue Date: 8/24/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P840368
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C40D010 EU4409027 4LBPSSQMB
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBPSSQ TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3039.0 lumens
Efficiency: N/A
Efficacy: 64.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P840368

CATALOG NUMBER: LDS4C40D010 EU4409027 4LBPSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P840368

CATALOG NUMBER: LDS4C40D010 EU4409027 4LBPSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	153967
5°	153442
10°	151757
15°	149150
20°	145807
25°	141905
30°	137431
35°	132150
40°	125479
45°	114091
50°	94179
55°	69358
60°	47067
65°	27557
70°	10890
75°	2461
80°	3167
85°	5425



TEST NUMBER: P840368

CATALOG NUMBER: LDS4C40D010 EU4409027 4LBPSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.1	4.9
10°-20°	420.4	13.8
20°-30°	613.2	20.2
30°-40°	700.0	23.0
40°-50°	636.4	20.9
50°-60°	375.3	12.4
60°-70°	125.9	4.1
70°-80°	13.2	0.4
80°-90°	4.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1183.7	39.0
0°-40°	1883.7	62.0
0°-60°	2895.4	95.3
0°-90°	3039.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3039.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1596	
5°	1584	150
15°	1493	420
25°	1333	613
35°	1122	700
45°	836	636
55°	412	375
65°	121	126
75°	7	13
85°	5	5
90°	0	



TEST NUMBER: P840368

CATALOG NUMBER: LDS4C40D010 EU4409027 4LBPSSQMB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1595.7
2.5°	1593.3
5°	1584.2
7.5°	1569.4
10°	1548.9
12.5°	1522.6
15°	1493.1
17.5°	1458.6
20°	1420.0
22.5°	1378.1
25°	1332.9
27.5°	1283.6
30°	1233.5
32.5°	1178.5
35°	1121.9
37.5°	1060.3
40°	996.2
42.5°	921.5
45°	836.1
47.5°	737.5
50°	627.4
52.5°	517.4
55°	412.3
57.5°	322.8
60°	243.9
62.5°	176.6
65°	120.7
67.5°	73.9
70°	38.6
72.5°	14.8
75°	6.6
77.5°	6.6
80°	5.7
82.5°	4.9
85°	4.9
87.5°	4.1
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)