

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840406

Luminaire Tested: **LDS4C55D010 EU4559050 4LBPSSQMB**

Issue Date: 8/24/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P840406
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C55D010 EU4559050 4LBSSQMB
Description: 4 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBSSQ TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4799.0 lumens
Efficiency: N/A
Efficacy: 75.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P840406

CATALOG NUMBER: LDS4C55D010 EU4559050 4LBPSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P840406

CATALOG NUMBER: LDS4C55D010 EU4559050 4LBPSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90																			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79																			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70																			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62																			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55																			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49																			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44																			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40																			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36																			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	243142
5°	242308
10°	239643
15°	235527
20°	230242
25°	224095
30°	217027
35°	208679
40°	198143
45°	180149
50°	148729
55°	109513
60°	74335
65°	43516
70°	17209
75°	3877
80°	5056
85°	8635



TEST NUMBER: P840406

CATALOG NUMBER: LDS4C55D010 EU4559050 4LBPSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	237.0	4.9
10°-20°	663.9	13.8
20°-30°	968.4	20.2
30°-40°	1105.4	23.0
40°-50°	1004.9	20.9
50°-60°	592.7	12.3
60°-70°	198.8	4.1
70°-80°	20.8	0.4
80°-90°	7.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1869.3	39.0
0°-40°	2974.7	62.0
0°-60°	4572.2	95.3
0°-90°	4799.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4799.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2520	
5°	2502	237
15°	2358	664
25°	2105	968
35°	1772	1105
45°	1320	1005
55°	651	593
65°	191	199
75°	10	21
85°	8	7
90°	0	



TEST NUMBER: P840406

CATALOG NUMBER: LDS4C55D010 EU4559050 4LBPSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2519.9
2.5°	2516.0
5°	2501.7
7.5°	2478.4
10°	2445.9
12.5°	2404.4
15°	2357.8
17.5°	2303.3
20°	2242.3
22.5°	2176.2
25°	2104.9
27.5°	2027.0
30°	1947.9
32.5°	1861.0
35°	1771.6
37.5°	1674.3
40°	1573.1
42.5°	1455.1
45°	1320.2
47.5°	1164.6
50°	990.8
52.5°	817.0
55°	651.0
57.5°	509.7
60°	385.2
62.5°	278.8
65°	190.6
67.5°	116.7
70°	61.0
72.5°	23.3
75°	10.4
77.5°	10.4
80°	9.1
82.5°	7.8
85°	7.8
87.5°	6.5
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)