

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840430

Luminaire Tested: **LDS4C70D010 EU4709030 4LBPSSQMB**

Issue Date: 8/24/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P840430
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C70D010 EU4709030 4LBPSSQMB
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBPSSQ TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5500.0 lumens
Efficiency: N/A
Efficacy: 70.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P840430

CATALOG NUMBER: LDS4C70D010 EU4709030 4LBPSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P840430

CATALOG NUMBER: LDS4C70D010 EU4709030 4LBPSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	278650
5°	277700
10°	274650
15°	269930
20°	263881
25°	256822
30°	248736
35°	239151
40°	227088
45°	206471
50°	170465
55°	125511
60°	85180
65°	49886
70°	19720
75°	4436
80°	5779
85°	9853



TEST NUMBER: P840430

CATALOG NUMBER: LDS4C70D010 EU4709030 4LBPSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.7	4.9
10°-20°	760.9	13.8
20°-30°	1109.8	20.2
30°-40°	1266.8	23.0
40°-50°	1151.7	20.9
50°-60°	679.2	12.3
60°-70°	227.8	4.1
70°-80°	23.8	0.4
80°-90°	8.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2142.4	39.0
0°-40°	3409.2	62.0
0°-60°	5240.1	95.3
0°-90°	5500.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5500.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2888	
5°	2867	272
15°	2702	761
25°	2412	1110
35°	2030	1267
45°	1513	1152
55°	746	679
65°	218	228
75°	12	24
85°	9	8
90°	0	



TEST NUMBER: P840430

CATALOG NUMBER: LDS4C70D010 EU4709030 4LBPSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2887.9
2.5°	2883.5
5°	2867.1
7.5°	2840.4
10°	2803.2
12.5°	2755.7
15°	2702.2
17.5°	2639.7
20°	2569.9
22.5°	2494.1
25°	2412.3
27.5°	2323.1
30°	2232.5
32.5°	2132.9
35°	2030.3
37.5°	1918.9
40°	1802.9
42.5°	1667.7
45°	1513.1
47.5°	1334.7
50°	1135.6
52.5°	936.4
55°	746.1
57.5°	584.1
60°	441.4
62.5°	319.6
65°	218.5
67.5°	133.8
70°	69.9
72.5°	26.8
75°	11.9
77.5°	11.9
80°	10.4
82.5°	8.9
85°	8.9
87.5°	7.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)