

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170437

Luminaire Tested: **LDA4A13827D010TE LAR25NF 4LA1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170437
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25629)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A13827D010TE LAR25NF 4LA1
Description: PORTFOLIO 4" Adjustable Reflector, Self-flange Trim Ring, 25° Narrow Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1228.4 lumens
Efficiency: N/A
Efficacy: 55.2 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.45
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 22.27
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170437

CATALOG NUMBER: LDA4A13827D010TE LAR25NF 4LA1

Luminous Intensity Polar Plot





TEST NUMBER: P170437

CATALOG NUMBER: LDA4A13827D010TE LAR25NF 4LA1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	95	94
3	108	104	100	97	106	102	99	97	100	97	95	98	96	94	96	94	92	91
4	105	100	96	93	103	99	95	93	97	94	92	95	93	91	93	91	90	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	88	91	89	87	86
6	99	93	89	86	98	93	89	86	91	88	85	90	87	85	89	86	84	83
7	97	90	86	83	95	90	86	83	89	85	83	88	85	83	87	84	82	81
8	94	88	84	81	93	87	83	81	86	83	81	85	82	80	85	82	80	79
9	92	85	81	79	91	85	81	79	84	81	78	83	80	78	83	80	78	77
10	89	83	79	76	89	83	79	76	82	79	76	81	78	76	81	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	684482
5°	600004
10°	447525
15°	284687
20°	150964
25°	34065
30°	8175
35°	2349
40°	805
45°	244
50°	134
55°	151
60°	173
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170437

CATALOG NUMBER: LDA4A13827D010TE LAR25NF 4LA1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	423.9	34.5
10°-20°	609.1	49.6
20°-30°	180.1	14.7
30°-40°	12.8	1.0
40°-50°	1.5	0.1
50°-60°	0.6	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1213.1	98.8
0°-40°	1225.9	99.8
0°-60°	1227.9	100.0
0°-90°	1228.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1228.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5549	
5°	4846	424
15°	2229	609
25°	250	180
35°	16	13
45°	1	1
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170437

CATALOG NUMBER: LDA4A13827D010TE LAR25NF 4LA1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5549.3
2.5°	5257.9
5°	4845.9
7.5°	4310.6
10°	3573.1
12.5°	2879.6
15°	2229.4
17.5°	1624.5
20°	1150.1
22.5°	728.2
25°	250.3
27.5°	109.2
30°	57.4
32.5°	29.1
35°	15.6
37.5°	9.2
40°	5.0
42.5°	2.8
45°	1.4
47.5°	0.7
50°	0.7
52.5°	0.7
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.0
67.5°	0.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)