

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170422

Luminaire Tested: **LDA4A18830D010TE LAR25NF 4LA1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170422
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25629)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A18830D010TE LAR25NF 4LA1
Description: PORTFOLIO 4" Adjustable Reflector, Self-flange Trim Ring, 25° Narrow Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1647.6 lumens
Efficiency: N/A
Efficacy: 56.6 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.45
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 29.12
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170422

CATALOG NUMBER: LDA4A18830D010TE LAR25NF 4LA1

Luminous Intensity Polar Plot





TEST NUMBER: P170422

CATALOG NUMBER: LDA4A18830D010TE LAR25NF 4LA1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97	97	97	97
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	95	94	94	94	94
3	108	104	100	97	106	102	99	97	100	97	95	98	96	94	96	94	92	91	91	91	91
4	105	100	96	93	103	99	95	93	97	94	92	95	93	91	93	91	90	88	88	88	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	88	91	89	87	86	86	86	86
6	99	93	89	86	98	93	89	86	91	88	85	90	87	85	89	86	84	83	83	83	83
7	97	90	86	83	95	90	86	83	89	85	83	88	85	83	87	84	82	81	81	81	81
8	94	88	84	81	93	87	83	81	86	83	81	85	82	80	85	82	80	79	79	79	79
9	92	85	81	79	91	85	81	79	84	81	78	83	80	78	83	80	78	77	77	77	77
10	89	83	79	76	89	83	79	76	82	79	76	81	78	76	81	78	76	75	75	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	917987
5°	804685
10°	600190
15°	381801
20°	202471
25°	45688
30°	10967
35°	3147
40°	1079
45°	331
50°	192
55°	215
60°	247
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170422

CATALOG NUMBER: LDA4A18830D010TE LAR25NF 4LA1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	568.5	34.5
10°-20°	816.8	49.6
20°-30°	241.6	14.7
30°-40°	17.1	1.0
40°-50°	2.0	0.1
50°-60°	0.9	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1626.9	98.7
0°-40°	1644.1	99.8
0°-60°	1646.9	100.0
0°-90°	1647.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1647.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7442	
5°	6499	569
15°	2990	817
25°	336	242
35°	21	17
45°	2	2
55°	1	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170422

CATALOG NUMBER: LDA4A18830D010TE LAR25NF 4LA1

CANDELA DISTRIBUTION (FULL):

	0°
0°	7442.4
2.5°	7051.6
5°	6499.0
7.5°	5781.0
10°	4792.0
12.5°	3861.9
15°	2989.9
17.5°	2178.7
20°	1542.5
22.5°	976.7
25°	335.7
27.5°	146.5
30°	77.0
32.5°	39.0
35°	20.9
37.5°	12.4
40°	6.7
42.5°	3.8
45°	1.9
47.5°	1.0
50°	1.0
52.5°	1.0
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	0.0
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)