

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170391

Luminaire Tested: **LDA4A18835D010TE LAR15SP 4LA1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25628)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A18835D010TE LAR15SP 4LA1
Description: PORTFOLIO 4" Adjustable Reflector, Self-flange Trim Ring, 15° Spot
Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1596.0 lumens
Efficiency: N/A
Efficacy: 54.8 lumens/watt
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.35
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 29.12
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170391

CATALOG NUMBER: LDA4A18835D010TE LAR15SP 4LA1

Luminous Intensity Polar Plot





TEST NUMBER: P170391

CATALOG NUMBER: LDA4A18835D010TE LAR15SP 4LA1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	105	102	104	102	100	101	100	98	98	97	96	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	97	95	94	92
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82
9	94	88	84	82	93	87	84	82	87	84	81	86	83	81	85	83	81	80
10	92	86	82	80	91	85	82	80	85	82	80	84	81	79	84	81	79	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1281450
5°	1069059
10°	581228
15°	308745
20°	175878
25°	34433
30°	7121
35°	2108
40°	805
45°	349
50°	192
55°	215
60°	247
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170391

CATALOG NUMBER: LDA4A18835D010TE LAR15SP 4LA1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	684.5	42.9
10°-20°	697.4	43.7
20°-30°	200.1	12.5
30°-40°	11.3	0.7
40°-50°	1.7	0.1
50°-60°	0.9	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1581.9	99.1
0°-40°	1593.3	99.8
0°-60°	1595.9	100.0
0°-90°	1596.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1596.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10389	
5°	8634	685
15°	2418	697
25°	253	200
35°	14	11
45°	2	2
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170391

CATALOG NUMBER: LDA4A18835D010TE LAR15SP 4LA1

CANDELA DISTRIBUTION (FULL):

	0°
0°	10389.1
2.5°	9959.1
5°	8634.2
7.5°	6468.4
10°	4640.6
12.5°	3346.7
15°	2417.8
17.5°	1749.8
20°	1339.9
22.5°	844.9
25°	253.0
27.5°	97.0
30°	50.0
32.5°	26.0
35°	14.0
37.5°	8.0
40°	5.0
42.5°	3.0
45°	2.0
47.5°	1.0
50°	1.0
52.5°	1.0
55°	1.0
57.5°	1.0
60°	1.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)