

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170487

Luminaire Tested: **LDA4A18835D010TE LAR15SP 4LAL1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P170487  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26144)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA4A18835D010TE LAR15SP 4LAL1  
Description: PORTFOLIO 4" Lensed Adjustable, Self-flange Trim Ring, 15° Spot  
Optic, at 0° tilt  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1749.0 lumens  
Efficiency: N/A  
Efficacy: 60.1 lumens/watt  
Spacing Criteria (0/90/45): 0.29 / 0.29 / 0.34  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 29.12  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P170487

CATALOG NUMBER: LDA4A18835D010TE LAR15SP 4LAL1

### Luminous Intensity Polar Plot





TEST NUMBER: P170487

CATALOG NUMBER: LDA4A18835D010TE LAR15SP 4LAL1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97																			
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	95																			
3	109	104	101	98	107	103	100	98	101	98	96	98	96	95	96	95	93	92																			
4	106	101	97	94	104	100	96	94	98	95	93	96	94	92	94	92	91	90																			
5	103	97	94	91	102	97	93	90	95	92	90	94	91	89	92	90	88	87																			
6	100	95	91	88	99	94	90	88	93	89	87	91	89	87	90	88	86	85																			
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83																			
8	95	89	86	83	95	89	85	83	88	85	83	87	84	82	86	84	82	81																			
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79																			
10	91	85	81	79	90	85	81	79	84	81	79	83	81	79	83	80	78	78																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1462891
5°	1143374
10°	624401
15°	341040
20°	191957
25°	48736
30°	9258
35°	3313
40°	1610
45°	872
50°	192
55°	215
60°	247
65°	292
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170487

CATALOG NUMBER: LDA4A18835D010TE LAR15SP 4LAL1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	729.9	41.7
10°-20°	758.7	43.4
20°-30°	238.0	13.6
30°-40°	16.7	1.0
40°-50°	3.9	0.2
50°-60°	0.9	0.1
60°-70°	0.9	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1726.6	98.7
0°-40°	1743.4	99.7
0°-60°	1748.1	100.0
0°-90°	1749.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1749.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11860	
5°	9234	730
15°	2671	759
25°	358	238
35°	22	17
45°	5	4
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170487

CATALOG NUMBER: LDA4A18835D010TE LAR15SP 4LAL1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11860.1
1°	11671.1
2°	11239.9
3°	10665.8
4°	10030.6
5°	9234.4
6°	8292.2
7°	7306.9
8°	6420.7
9°	5649.5
10°	4985.3
11°	4404.2
12°	3894.0
13°	3442.9
14°	3036.8
15°	2670.7
17.5°	1928.5
20°	1462.4
22.5°	995.3
25°	358.1
27.5°	120.0
30°	65.0
32.5°	36.0
35°	22.0
37.5°	15.0
40°	10.0
42.5°	7.0
45°	5.0
47.5°	3.0
50°	1.0
52.5°	1.0
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P170487

CATALOG NUMBER: LDA4A18835D010TE LAR15SP 4LAL1

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)