

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170416

Luminaire Tested: **LDA4A28840D010TE LAR15SP 4LA1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170416
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25628)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A28840D010TE LAR15SP 4LA1
Description: PORTFOLIO 4" Adjustable Reflector, Self-flange Trim Ring, 15° Spot
Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2563.1 lumens
Efficiency: N/A
Efficacy: 57.6 lumens/watt
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.35
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 44.49
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170416
CATALOG NUMBER: LDA4A28840D010TE LAR15SP 4LA1

Luminous Intensity Polar Plot





TEST NUMBER: P170416

CATALOG NUMBER: LDA4A28840D010TE LAR15SP 4LA1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	105	102	104	102	100	101	100	98	98	97	96	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	97	95	94	92
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82
9	94	88	84	82	93	87	84	82	87	84	81	86	83	81	85	83	81	80
10	92	86	82	80	91	85	82	80	85	82	80	84	81	79	84	81	79	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2057911
5°	1716831
10°	933401
15°	495821
20°	282449
25°	55296
30°	11437
35°	3388
40°	1288
45°	558
50°	307
55°	344
60°	395
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170416

CATALOG NUMBER: LDA4A28840D010TE LAR15SP 4LA1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1099.3	42.9
10°-20°	1119.9	43.7
20°-30°	321.3	12.5
30°-40°	18.2	0.7
40°-50°	2.7	0.1
50°-60°	1.4	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2540.5	99.1
0°-40°	2558.7	99.8
0°-60°	2562.9	100.0
0°-90°	2563.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2563.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16684	
5°	13866	###
15°	3883	1120
25°	406	321
35°	22	18
45°	3	3
55°	2	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170416

CATALOG NUMBER: LDA4A28840D010TE LAR15SP 4LA1

CANDELA DISTRIBUTION (FULL):

	0°
0°	16684.1
2.5°	15993.6
5°	13865.9
7.5°	10387.8
10°	7452.4
12.5°	5374.6
15°	3882.8
17.5°	2810.1
20°	2151.8
22.5°	1356.9
25°	406.3
27.5°	155.8
30°	80.3
32.5°	41.8
35°	22.5
37.5°	12.8
40°	8.0
42.5°	4.8
45°	3.2
47.5°	1.6
50°	1.6
52.5°	1.6
55°	1.6
57.5°	1.6
60°	1.6
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)