

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170433

Luminaire Tested: **LDA4A09927D010TE LAR25NF 4LA1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170433
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25629)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A09927D010TE LAR25NF 4LA1
Description: PORTFOLIO 4" Adjustable Reflector, Self-flange Trim Ring, 25° Narrow Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 664.8 lumens
Efficiency: N/A
Efficacy: 48.0 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.45
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 13.84
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170433

CATALOG NUMBER: LDA4A09927D010TE LAR25NF 4LA1

Luminous Intensity Polar Plot





TEST NUMBER: P170433

CATALOG NUMBER: LDA4A09927D010TE LAR25NF 4LA1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97	98	96	95	94	94	92	91	91	90	88																		
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	94	96	94	92	91	90	88	87	86	84	83																			
3	108	104	100	97	106	102	99	97	100	97	95	98	96	94	96	94	92	91	90	88	87	86	84	83	81	80	79																			
4	105	100	96	93	103	99	95	93	97	94	92	95	93	91	93	91	90	88	87	86	84	83	81	80	78	77	76																			
5	102	96	92	89	101	95	92	89	94	91	88	92	90	88	91	89	87	86	84	83	81	80	78	77	76	75	74																			
6	99	93	89	86	98	93	89	86	91	88	85	90	87	85	89	86	84	83	81	80	78	77	76	75	74	73	72																			
7	97	90	86	83	95	90	86	83	89	85	83	88	85	83	87	84	82	81	80	78	77	76	75	74	73	72	71																			
8	94	88	84	81	93	87	83	81	86	83	81	85	82	80	85	82	80	79	78	77	76	75	74	73	72	71	70																			
9	92	85	81	79	91	85	81	79	84	81	78	83	80	78	83	80	78	77	76	75	74	73	72	71	70	69	68																			
10	89	83	79	76	89	83	79	76	82	79	76	81	78	76	81	78	76	75	74	73	72	71	70	69	68	67	66																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	370395
5°	324685
10°	242168
15°	154053
20°	81697
25°	18428
30°	4429
35°	1265
40°	435
45°	140
50°	77
55°	86
60°	99
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170433

CATALOG NUMBER: LDA4A09927D010TE LAR25NF 4LA1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.4	34.5
10°-20°	329.6	49.6
20°-30°	97.5	14.7
30°-40°	6.9	1.0
40°-50°	0.8	0.1
50°-60°	0.4	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	656.4	98.7
0°-40°	663.4	99.8
0°-60°	664.5	100.0
0°-90°	664.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	664.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3003	
5°	2622	229
15°	1206	330
25°	135	97
35°	8	7
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170433

CATALOG NUMBER: LDA4A09927D010TE LAR25NF 4LA1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3002.9
2.5°	2845.2
5°	2622.3
7.5°	2332.6
10°	1933.5
12.5°	1558.3
15°	1206.4
17.5°	879.1
20°	622.4
22.5°	394.1
25°	135.4
27.5°	59.1
30°	31.1
32.5°	15.7
35°	8.4
37.5°	5.0
40°	2.7
42.5°	1.5
45°	0.8
47.5°	0.4
50°	0.4
52.5°	0.4
55°	0.4
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.0
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)