

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170434

Luminaire Tested: **LDA4A09930D010TE LAR25NF 4LA1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P170434  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25629)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA4A09930D010TE LAR25NF 4LA1  
Description: PORTFOLIO 4" Adjustable Reflector, Self-flange Trim Ring, 25° Narrow Flood Optic, at 0° tilt  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 766.2 lumens  
Efficiency: N/A  
Efficacy: 55.4 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.45  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.84  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P170434

CATALOG NUMBER: LDA4A09930D010TE LAR25NF 4LA1

### Luminous Intensity Polar Plot





TEST NUMBER: P170434

CATALOG NUMBER: LDA4A09930D010TE LAR25NF 4LA1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97	97	97	97
2	112	108	105	103	110	106	104	102	103	101	99	100	99	97	98	96	95	94	94	94	94
3	108	104	100	97	106	102	99	97	100	97	95	98	96	94	96	94	92	91	91	91	91
4	105	100	96	93	103	99	95	93	97	94	92	95	93	91	93	91	90	88	88	88	88
5	102	96	92	89	101	96	92	89	94	91	88	92	90	88	91	89	87	86	86	86	86
6	99	93	89	86	98	93	89	86	91	88	85	90	87	85	89	86	84	83	83	83	83
7	97	90	86	83	95	90	86	83	89	85	83	88	85	83	87	84	82	81	81	81	81
8	94	88	84	81	93	87	83	81	86	83	81	85	82	80	85	82	80	79	79	79	79
9	92	85	81	79	91	85	81	79	84	81	78	83	80	78	83	80	78	77	77	77	77
10	89	83	79	76	89	83	79	76	82	79	76	81	78	76	81	78	76	75	75	75	75

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	426973
5°	374273
10°	279154
15°	177588
20°	94167
25°	21245
30°	5099
35°	1461
40°	499
45°	157
50°	77
55°	86
60°	99
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170434

CATALOG NUMBER: LDA4A09930D010TE LAR25NF 4LA1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	264.4	34.5
10°-20°	379.9	49.6
20°-30°	112.3	14.7
30°-40°	8.0	1.0
40°-50°	0.9	0.1
50°-60°	0.4	0.0
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	756.7	98.8
0°-40°	764.7	99.8
0°-60°	765.9	100.0
0°-90°	766.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	766.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3462	
5°	3023	264
15°	1391	380
25°	156	112
35°	10	8
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170434

CATALOG NUMBER: LDA4A09930D010TE LAR25NF 4LA1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3461.6
2.5°	3279.8
5°	3022.8
7.5°	2688.9
10°	2228.8
12.5°	1796.3
15°	1390.7
17.5°	1013.4
20°	717.4
22.5°	454.3
25°	156.1
27.5°	68.1
30°	35.8
32.5°	18.1
35°	9.7
37.5°	5.8
40°	3.1
42.5°	1.8
45°	0.9
47.5°	0.4
50°	0.4
52.5°	0.4
55°	0.4
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.0
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)