

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170467

Luminaire Tested: **LDA4A09935D010TE LAR35FL 4LA1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P170467  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25630)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA4A09935D010TE LAR35FL 4LA1  
Description: PORTFOLIO 4" Adjustable Reflector, Self-flange Trim Ring, 35° Flood Optic, at 0° tilt  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 800.2 lumens  
Efficiency: N/A  
Efficacy: 57.8 lumens/watt  
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.54  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.84  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P170467

CATALOG NUMBER: LDA4A09935D010TE LAR35FL 4LA1

### Luminous Intensity Polar Plot





TEST NUMBER: P170467

CATALOG NUMBER: LDA4A09935D010TE LAR35FL 4LA1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	97	97	96	95	93	92	90	88	87	85	84	81																
2	111	108	104	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93	95	93	91	90	88	87	85	84	81																		
3	108	103	99	96	106	102	98	96	99	96	94	97	95	93	95	93	91	90	92	90	88	87	85	84	81																				
4	104	99	95	92	103	98	94	91	96	93	90	94	91	89	92	90	88	87	92	90	88	87	85	84	81																				
5	101	95	91	88	100	94	90	87	93	89	87	91	88	86	90	87	85	84	90	87	85	84	81																						
6	98	92	87	84	97	91	87	84	90	86	84	88	85	83	87	85	83	81	87	85	83	81																							
7	95	88	84	81	94	88	84	81	87	83	81	86	83	80	85	82	80	79	85	82	80	79																							
8	92	86	81	78	91	85	81	78	84	81	78	83	80	78	82	80	77	76	82	80	77	76																							
9	90	83	79	76	89	82	79	76	82	78	76	81	78	75	80	77	75	74	80	77	75	74																							
10	87	80	76	74	86	80	76	73	79	76	73	79	75	73	78	75	73	72	78	75	73	72																							

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	326299
5°	307239
10°	258074
15°	201237
20°	121483
25°	28158
30°	7363
35°	1747
40°	580
45°	157
50°	77
55°	86
60°	99
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170467

CATALOG NUMBER: LDA4A09935D010TE LAR35FL 4LA1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	223.5	27.9
10°-20°	420.9	52.6
20°-30°	144.1	18.0
30°-40°	10.3	1.3
40°-50°	1.0	0.1
50°-60°	0.4	0.0
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	788.5	98.5
0°-40°	798.7	99.8
0°-60°	800.1	100.0
0°-90°	800.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	800.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2645	
5°	2481	223
15°	1576	421
25°	207	144
35°	12	10
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170467

CATALOG NUMBER: LDA4A09935D010TE LAR35FL 4LA1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2645.4
2.5°	2586.1
5°	2481.4
7.5°	2304.0
10°	2060.5
12.5°	1824.3
15°	1575.9
17.5°	1274.6
20°	925.5
22.5°	552.8
25°	206.9
27.5°	100.8
30°	51.7
32.5°	23.2
35°	11.6
37.5°	6.2
40°	3.6
42.5°	1.8
45°	0.9
47.5°	0.4
50°	0.4
52.5°	0.4
55°	0.4
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)