

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P855851

Luminaire Tested: **LD4C70D010 EU4709050 4LBMLI**

Issue Date: 7/19/2024

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P855851  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/19/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C70D010 EU4709050 4LBMLI  
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 4LBM TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6813.0 lumens  
Efficiency: N/A  
Efficacy: 87.3 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 78  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P855851

CATALOG NUMBER: LD4C70D010 EU4709050 4LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P855851

CATALOG NUMBER: LD4C70D010 EU4709050 4LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1319483
5°	1297059
10°	1191787
15°	998064
20°	799606
25°	642471
30°	478263
35°	273227
40°	128235
45°	54450
50°	17335
55°	8825
60°	6069
65°	4796
70°	2945
75°	0
80°	0
85°	0



TEST NUMBER: P855851

CATALOG NUMBER: LD4C70D010 EU4709050 4LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	972.5	14.3
10°-20°	2174.1	31.9
20°-30°	2161.5	31.7
30°-40°	1177.1	17.3
40°-50°	272.1	4.0
50°-60°	38.3	0.6
60°-70°	14.2	0.2
70°-80°	3.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5308.1	77.9
0°-40°	6485.2	95.2
0°-60°	6795.5	99.7
0°-90°	6813.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6813.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10740	
5°	10518	972
15°	7847	2174
25°	4740	2162
35°	1822	1177
45°	313	272
55°	41	38
65°	16	14
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P855851

CATALOG NUMBER: LD4C70D010 EU4709050 4LBMLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10740.3
2.5°	10715.5
5°	10517.6
7.5°	10113.9
10°	9553.5
12.5°	8729.2
15°	7847.2
17.5°	6973.4
20°	6116.1
22.5°	5415.5
25°	4739.6
27.5°	4096.8
30°	3371.4
32.5°	2563.6
35°	1821.8
37.5°	1228.0
40°	799.6
42.5°	502.7
45°	313.4
47.5°	181.4
50°	90.7
52.5°	49.5
55°	41.2
57.5°	24.7
60°	24.7
62.5°	16.5
65°	16.5
67.5°	8.2
70°	8.2
72.5°	8.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)