

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P777069

Luminaire Tested: LERS4D02D010-EC4DR300210IC9040-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P777069
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS4D02D010-EC4DR300210IC9040-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 388.6 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P777069

CATALOG NUMBER: LERS4D02D010-EC4DR300210IC9040-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P777069

CATALOG NUMBER: LERS4D02D010-EC4DR300210IC9040-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	95656	95656	95656
5°	92910	92802	92918
10°	80476	79900	80460
15°	52507	52222	51960
20°	26107	27084	26074
25°	13150	14831	12880
30°	5268	5736	4587
35°	2439	2336	1962
40°	1049	1169	989
45°	747	920	747
50°	250	679	274
55°	147	280	147
60°	107	122	107
65°	54	54	54
70°	45	22	45
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 920 cd/sqm



TEST NUMBER: P777069

CATALOG NUMBER: LERS4D02D010-EC4DR300210IC9040-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.9	28.3
10°-20°	177.0	45.5
20°-30°	76.5	19.7
30°-40°	17.4	4.5
40°-50°	6.0	1.5
50°-60°	1.5	0.4
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	363.3	93.5
0°-40°	380.8	98.0
0°-60°	388.2	99.9
0°-90°	388.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	388.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1250	1250	1250	1250	1250	
5°	1209	1208	1208	1210	1209	110
15°	663	655	659	657	656	177
25°	156	162	176	158	152	75
35°	26	27	25	25	21	18
45°	7	8	8	8	7	5
55°	1	1	2	1	1	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P777069

CATALOG NUMBER: LERS4D02D010-EC4DR300210IC9040-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1249.7	1249.7	1249.7	1249.7	1249.7
2.5°	1241.4	1240.6	1241.0	1241.6	1241.9
5°	1209.2	1208.0	1207.8	1210.3	1209.3
7.5°	1144.2	1142.6	1140.1	1145.7	1151.1
10°	1035.4	1033.5	1028.0	1030.8	1035.2
12.5°	874.7	868.7	868.6	877.2	876.0
15°	662.6	654.6	659.0	656.9	655.7
17.5°	445.6	442.5	448.4	446.6	438.9
20°	320.5	321.3	332.5	326.9	320.1
22.5°	233.9	236.7	250.1	235.5	230.2
25°	155.7	161.6	175.6	157.5	152.5
27.5°	95.8	98.5	112.6	94.5	91.8
30°	59.6	58.2	64.9	55.7	51.9
32.5°	39.1	37.4	39.5	35.5	32.4
35°	26.1	26.7	25.0	24.9	21.0
37.5°	16.3	18.8	16.6	17.6	13.5
40°	10.5	13.6	11.7	12.9	9.9
42.5°	8.7	10.5	9.6	10.3	8.8
45°	6.9	8.5	8.5	8.5	6.9
47.5°	3.8	5.7	7.3	5.8	4.1
50°	2.1	2.9	5.7	3.0	2.3
52.5°	1.5	1.7	3.8	1.7	1.5
55°	1.1	1.1	2.1	1.2	1.1
57.5°	0.9	0.9	1.1	0.9	0.9
60°	0.7	0.7	0.8	0.7	0.7
62.5°	0.5	0.5	0.6	0.5	0.5
65°	0.3	0.3	0.3	0.3	0.3
67.5°	0.2	0.2	0.2	0.2	0.2
70°	0.2	0.1	0.1	0.1	0.2
72.5°	0.1	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)