

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P#

Luminaire Tested: **LD4C75D010 EX4C759027 4LBSQH**

Issue Date: 2/9/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C75D010 EX4C759027 4LBSQH
Description: 4 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBSQ TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6309.0 lumens
Efficiency: N/A
Efficacy: 77.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P#
CATALOG NUMBER: LD4C75D010 EX4C759027 4LBSQH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD4C75D010 EX4C759027 4LBSQH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85																			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79																			
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73																			
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67																			
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62																			
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58																			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54																			
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50																			
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	603615
5°	594850
10°	569993
15°	538361
20°	502522
25°	456176
30°	380864
35°	275914
40°	172725
45°	98726
50°	51473
55°	28850
60°	18391
65°	10868
70°	8068
75°	3542
80°	5279
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD4C75D010 EX4C759027 4LBSQH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	575.6	9.1
10°-20°	1510.1	23.9
20°-30°	1940.8	30.8
30°-40°	1460.2	23.1
40°-50°	586.4	9.3
50°-60°	166.7	2.6
60°-70°	52.8	0.8
70°-80°	15.0	0.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4026.5	63.8
0°-40°	5486.7	87.0
0°-60°	6239.9	98.9
0°-90°	6309.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6309.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6256	
5°	6142	576
15°	5389	1510
25°	4285	1941
35°	2342	1460
45°	724	586
55°	172	167
65°	48	53
75°	10	15
85°	0	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD4C75D010 EX4C759027 4LBSQH

CANDELA DISTRIBUTION (FULL):

	0°
0°	6255.8
2.5°	6217.7
5°	6141.5
7.5°	5998.6
10°	5817.6
12.5°	5598.9
15°	5389.4
17.5°	5151.2
20°	4894.0
22.5°	4618.2
25°	4284.8
27.5°	3884.7
30°	3418.4
32.5°	2894.5
35°	2342.4
37.5°	1828.1
40°	1371.3
42.5°	1009.3
45°	723.5
47.5°	495.3
50°	342.9
52.5°	238.1
55°	171.5
57.5°	123.8
60°	95.3
62.5°	66.7
65°	47.6
67.5°	38.1
70°	28.6
72.5°	19.1
75°	9.5
77.5°	9.5
80°	9.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)