

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P777074

Luminaire Tested: LERS4D02D010-EC4DR300210IC9050-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P777074
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS4D02D010-EC4DR300210IC9050-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 403.3 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P777074

CATALOG NUMBER: LERS4D02D010-EC4DR300210IC9050-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P777074

CATALOG NUMBER: LERS4D02D010-EC4DR300210IC9050-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	99254	99254	99254
5°	96406	96291	96414
10°	83499	82908	83484
15°	54480	54187	53917
20°	27092	28102	27051
25°	13648	15388	13361
30°	5462	5957	4764
35°	2532	2429	2037
40°	1089	1209	1029
45°	769	953	779
50°	262	691	274
55°	147	294	160
60°	107	122	107
65°	72	72	72
70°	45	22	45
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 953 cd/sqm



TEST NUMBER: P777074

CATALOG NUMBER: LERS4D02D010-EC4DR300210IC9050-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.0	28.3
10°-20°	183.6	45.5
20°-30°	79.4	19.7
30°-40°	18.1	4.5
40°-50°	6.2	1.5
50°-60°	1.5	0.4
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	377.0	93.5
0°-40°	395.1	98.0
0°-60°	402.8	99.9
0°-90°	403.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	403.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1297	1297	1297	1297	1297	
5°	1255	1254	1253	1256	1255	114
15°	688	679	684	682	680	184
25°	162	168	182	163	158	77
35°	27	28	26	26	22	18
45°	7	9	9	9	7	5
55°	1	1	2	1	1	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P777074

CATALOG NUMBER: LERS4D02D010-EC4DR300210IC9050-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1296.7	1296.7	1296.7	1296.7	1296.7
2.5°	1288.1	1287.2	1287.7	1288.3	1288.6
5°	1254.7	1253.5	1253.2	1255.9	1254.8
7.5°	1187.3	1185.5	1182.9	1188.9	1194.4
10°	1074.3	1072.4	1066.7	1069.5	1074.1
12.5°	907.6	901.4	901.3	910.2	909.0
15°	687.5	679.2	683.8	681.6	680.4
17.5°	462.3	459.2	465.2	463.4	455.4
20°	332.6	333.4	345.0	339.2	332.1
22.5°	242.7	245.7	259.5	244.4	238.9
25°	161.6	167.7	182.2	163.4	158.2
27.5°	99.4	102.2	116.9	98.1	95.3
30°	61.8	60.4	67.4	57.8	53.9
32.5°	40.6	38.8	41.0	36.8	33.6
35°	27.1	27.7	26.0	25.8	21.8
37.5°	17.0	19.5	17.2	18.3	14.0
40°	10.9	14.2	12.1	13.4	10.3
42.5°	9.0	10.9	10.0	10.7	9.2
45°	7.1	8.8	8.8	8.8	7.2
47.5°	4.0	5.9	7.6	6.1	4.2
50°	2.2	3.0	5.8	3.1	2.3
52.5°	1.5	1.7	4.0	1.8	1.6
55°	1.1	1.2	2.2	1.3	1.2
57.5°	0.9	1.0	1.1	1.0	0.9
60°	0.7	0.7	0.8	0.7	0.7
62.5°	0.5	0.5	0.6	0.5	0.5
65°	0.4	0.4	0.4	0.4	0.4
67.5°	0.2	0.2	0.2	0.2	0.2
70°	0.2	0.1	0.1	0.1	0.2
72.5°	0.1	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)