

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P#

Luminaire Tested: **LD4C80D010 EX4C809035 4LBSQH**

Issue Date: 2/9/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C80D010 EX4C809035 4LBSQH
Description: 4 INCH 8000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBSQ TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7185.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 89.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P#
CATALOG NUMBER: LD4C80D010 EX4C809035 4LBSQH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD4C80D010 EX4C809035 4LBSQH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73			73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67			67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	687425
5°	677440
10°	649139
15°	613111
20°	572305
25°	519522
30°	433753
35°	314232
40°	196708
45°	112440
50°	58618
55°	32854
60°	20938
65°	12375
70°	9169
75°	4026
80°	6001
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD4C80D010 EX4C809035 4LBSQH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	655.6	9.1
10°-20°	1719.8	23.9
20°-30°	2210.3	30.8
30°-40°	1662.9	23.1
40°-50°	667.9	9.3
50°-60°	189.9	2.6
60°-70°	60.1	0.8
70°-80°	17.1	0.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4585.6	63.8
0°-40°	6248.6	87.0
0°-60°	7106.3	98.9
0°-90°	7185.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7185.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7124	
5°	6994	656
15°	6138	1720
25°	4880	2210
35°	2668	1663
45°	824	668
55°	195	190
65°	54	60
75°	11	17
85°	0	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD4C80D010 EX4C809035 4LBSQH

CANDELA DISTRIBUTION (FULL):

	0°
0°	7124.4
2.5°	7081.0
5°	6994.2
7.5°	6831.5
10°	6625.4
12.5°	6376.3
15°	6137.7
17.5°	5866.5
20°	5573.6
22.5°	5259.5
25°	4879.8
27.5°	4424.1
30°	3893.1
32.5°	3296.4
35°	2667.7
37.5°	2081.9
40°	1561.7
42.5°	1149.4
45°	824.0
47.5°	564.1
50°	390.5
52.5°	271.2
55°	195.3
57.5°	141.0
60°	108.5
62.5°	75.9
65°	54.2
67.5°	43.4
70°	32.5
72.5°	21.7
75°	10.8
77.5°	10.8
80°	10.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)