

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P777683

Luminaire Tested: LERS4D08D010-EC4DR300210IC9027-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P777683
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS4D08D010-EC4DR300210IC9027-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 707.4 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P777683

CATALOG NUMBER: LERS4D08D010-EC4DR300210IC9027-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P777683

CATALOG NUMBER: LERS4D08D010-EC4DR300210IC9027-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96								
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92								
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89								
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85								
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82								
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79								
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77								
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74								
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72								
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	174106	174106	174106
5°	169108	168908	169116
10°	146471	145438	146432
15°	95560	95053	94577
20°	47521	49305	47456
25°	23935	26992	23445
30°	9590	10438	8352
35°	4448	4252	3569
40°	1918	2128	1809
45°	1353	1678	1364
50°	464	1227	488
55°	267	507	280
60°	184	214	184
65°	127	127	127
70°	67	45	67
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 1678 cd/sqm



TEST NUMBER: P777683

CATALOG NUMBER: LERS4D08D010-EC4DR300210IC9027-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.0	28.3
10°-20°	322.1	45.5
20°-30°	139.2	19.7
30°-40°	31.7	4.5
40°-50°	10.9	1.5
50°-60°	2.7	0.4
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	661.3	93.5
0°-40°	693.1	98.0
0°-60°	706.6	99.9
0°-90°	707.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	707.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2275	2275	2275	2275	2275	
5°	2201	2199	2198	2203	2201	200
15°	1206	1192	1200	1196	1194	323
25°	283	294	320	287	278	136
35°	48	49	46	45	38	32
45°	12	16	16	16	13	9
55°	2	2	4	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P777683

CATALOG NUMBER: LERS4D08D010-EC4DR300210IC9027-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2274.6	2274.6	2274.6	2274.6	2274.6
2.5°	2259.5	2257.9	2258.9	2259.9	2260.4
5°	2200.9	2198.8	2198.3	2202.9	2201.0
7.5°	2082.6	2079.6	2075.0	2085.4	2095.1
10°	1884.5	1881.2	1871.2	1876.1	1884.0
12.5°	1592.0	1581.2	1580.9	1596.6	1594.5
15°	1205.9	1191.5	1199.5	1195.6	1193.5
17.5°	811.0	805.4	816.1	812.9	798.9
20°	583.4	584.8	605.3	595.0	582.6
22.5°	425.7	431.0	455.2	428.7	419.0
25°	283.4	294.2	319.6	286.6	277.6
27.5°	174.3	179.2	205.1	172.1	167.2
30°	108.5	106.0	118.1	101.4	94.5
32.5°	71.2	68.0	71.9	64.6	59.0
35°	47.6	48.6	45.5	45.2	38.2
37.5°	29.7	34.1	30.1	32.1	24.6
40°	19.2	24.8	21.3	23.5	18.1
42.5°	15.8	19.1	17.5	18.7	16.1
45°	12.5	15.5	15.5	15.5	12.6
47.5°	6.9	10.4	13.3	10.6	7.4
50°	3.9	5.3	10.3	5.5	4.1
52.5°	2.7	3.0	7.0	3.2	2.8
55°	2.0	2.1	3.8	2.2	2.1
57.5°	1.5	1.7	2.0	1.7	1.5
60°	1.2	1.2	1.4	1.3	1.2
62.5°	0.9	0.9	1.0	0.9	0.9
65°	0.7	0.7	0.7	0.7	0.7
67.5°	0.3	0.5	0.5	0.5	0.5
70°	0.3	0.2	0.2	0.2	0.3
72.5°	0.2	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)