

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P777900

Luminaire Tested: LERS4D10D010-EC4DR100210IC9030-4LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P777900
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS4D10D010-EC4DR100210IC9030-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 10° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 981.0 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.17 / 0.17 / 0.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P777900
CATALOG NUMBER: LERS4D10D010-EC4DR100210IC9030-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P777900

CATALOG NUMBER: LERS4D10D010-EC4DR100210IC9030-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	98
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	100	99	98	97
3	111	107	104	102	109	106	103	101	103	101	99	101	99	98	99	98	96	95
4	108	104	101	99	107	103	100	98	101	99	97	99	97	96	98	96	95	94
5	106	102	99	96	105	101	98	96	99	97	95	98	96	94	97	95	94	93
6	104	100	96	94	103	99	96	94	98	95	93	97	94	93	96	94	92	91
7	103	98	95	93	102	97	94	92	96	94	92	95	93	92	95	93	91	90
8	101	96	93	91	100	96	93	91	95	92	91	94	92	90	93	92	90	89
9	100	95	92	90	99	94	92	90	94	91	90	93	91	89	93	91	89	88
10	98	94	91	89	98	93	91	89	93	90	88	92	90	88	92	90	88	87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2333886
5°	1106718
10°	226974
15°	62315
20°	25115
25°	13454
30°	7961
35°	5175
40°	3466
45°	2256
50°	1241
55°	933
60°	524
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2256 cd/sqm



TEST NUMBER: P777900

CATALOG NUMBER: LERS4D10D010-EC4DR100210IC9030-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	697.6	71.1
10°-20°	188.8	19.2
20°-30°	54.0	5.5
30°-40°	24.7	2.5
40°-50°	11.3	1.2
50°-60°	3.8	0.4
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	940.4	95.9
0°-40°	965.1	98.4
0°-60°	980.2	99.9
0°-90°	981.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	981.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	21361	
5°	10091	698
15°	551	189
25°	112	54
35°	39	25
45°	15	11
55°	5	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P777900

CATALOG NUMBER: LERS4D10D010-EC4DR100210IC9030-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	21360.7
0.5°	21176.2
1°	20703.0
1.5°	19790.5
2°	18768.8
2.5°	17419.5
3°	15919.8
3.5°	14468.6
4°	12903.3
4.5°	11461.8
5°	10090.6
5.5°	8848.1
6°	7663.8
6.5°	6622.7
7°	5642.3
7.5°	4805.1
8°	4062.5
8.5°	3412.1
9°	2849.1
9.5°	2419.5
10°	2045.8
12.5°	975.6
15°	550.9
17.5°	334.9
20°	216.0
22.5°	150.5
25°	111.6
27.5°	82.5
30°	63.1
32.5°	48.5
35°	38.8
37.5°	29.1
40°	24.3
42.5°	19.4
45°	14.6
47.5°	9.7
50°	7.3
52.5°	4.9
55°	4.9
57.5°	2.4
60°	2.4
62.5°	2.4
65°	0.0



TEST NUMBER: P777900

CATALOG NUMBER: LERS4D10D010-EC4DR100210IC9030-4LBS1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		0.0
70°		0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)