

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840322

Luminaire Tested: **LDS4C15D010 EU4159035 4LBPSSQMB**

Issue Date: 8/24/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P840322  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C15D010 EU4159035 4LBPSSQMB  
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 4LBPSSQ TRIM WITH MB FINISH  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1229.0 lumens  
Efficiency: N/A  
Efficacy: 77.8 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P840322

CATALOG NUMBER: LDS4C15D010 EU4159035 4LBPSSQMB

### Luminous Intensity Polar Plot





TEST NUMBER: P840322

CATALOG NUMBER: LDS4C15D010 EU4159035 4LBPSSQMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	62264
5°	62057
10°	61373
15°	60315
20°	58960
25°	57384
30°	55585
35°	53442
40°	50748
45°	46136
50°	38083
55°	28043
60°	19028
65°	11142
70°	4401
75°	1007
80°	1278
85°	2214



TEST NUMBER: P840322

CATALOG NUMBER: LDS4C15D010 EU4159035 4LBPSSQMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	60.7	4.9
10°-20°	170.0	13.8
20°-30°	248.0	20.2
30°-40°	283.1	23.0
40°-50°	257.3	20.9
50°-60°	151.8	12.3
60°-70°	50.9	4.1
70°-80°	5.3	0.4
80°-90°	1.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	478.7	39.0
0°-40°	761.8	62.0
0°-60°	1170.9	95.3
0°-90°	1229.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1229.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	645	
5°	641	61
15°	604	170
25°	539	248
35°	454	283
45°	338	257
55°	167	152
65°	49	51
75°	3	5
85°	2	2
90°	0	



TEST NUMBER: P840322

CATALOG NUMBER: LDS4C15D010 EU4159035 4LBPSSQMB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	645.3
2.5°	644.3
5°	640.7
7.5°	634.7
10°	626.4
12.5°	615.8
15°	603.8
17.5°	589.9
20°	574.2
22.5°	557.3
25°	539.0
27.5°	519.1
30°	498.9
32.5°	476.6
35°	453.7
37.5°	428.8
40°	402.9
42.5°	372.6
45°	338.1
47.5°	298.3
50°	253.7
52.5°	209.2
55°	166.7
57.5°	130.5
60°	98.6
62.5°	71.4
65°	48.8
67.5°	29.9
70°	15.6
72.5°	6.0
75°	2.7
77.5°	2.7
80°	2.3
82.5°	2.0
85°	2.0
87.5°	1.7
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)