

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P777905

Luminaire Tested: LERS4D10D010-EC4DR100210IC9035-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P777905
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS4D10D010-EC4DR100210IC9035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 10° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1099.3 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 0.17 / 0.17 / 0.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P777905
CATALOG NUMBER: LERS4D10D010-EC4DR100210IC9035-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P777905

CATALOG NUMBER: LERS4D10D010-EC4DR100210IC9035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	98	98	98	98
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	100	99	98	97	97	97	97
3	111	107	104	102	109	106	103	101	103	101	99	101	99	98	99	98	96	95	95	95	95
4	108	104	101	99	107	103	100	98	101	99	97	99	97	96	98	96	95	94	94	94	94
5	106	102	99	96	105	101	98	96	99	97	95	98	96	94	97	95	94	93	93	93	93
6	104	100	96	94	103	99	96	94	98	95	93	97	94	93	96	94	92	91	91	91	91
7	103	98	95	93	102	97	94	92	96	94	92	95	93	92	95	93	91	90	90	90	90
8	101	96	93	91	100	96	93	91	95	92	91	94	92	90	93	92	90	89	89	89	89
9	100	95	92	90	99	94	92	90	94	91	90	93	91	89	93	91	89	88	88	88	88
10	98	94	91	89	98	93	91	89	93	90	88	92	90	88	92	90	88	87	87	87	87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2615298
5°	1240163
10°	254344
15°	69826
20°	28138
25°	15082
30°	8920
35°	5802
40°	3880
45°	2519
50°	1394
55°	1029
60°	590
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2519 cd/sqm



TEST NUMBER: P777905

CATALOG NUMBER: LERS4D10D010-EC4DR100210IC9035-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	781.7	71.1
10°-20°	211.5	19.2
20°-30°	60.6	5.5
30°-40°	27.6	2.5
40°-50°	12.7	1.2
50°-60°	4.2	0.4
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1053.8	95.9
0°-40°	1081.4	98.4
0°-60°	1098.3	99.9
0°-90°	1099.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1099.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23936	
5°	11307	782
15°	617	212
25°	125	61
35°	44	28
45°	16	13
55°	5	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P777905

CATALOG NUMBER: LERS4D10D010-EC4DR100210IC9035-4LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	23936.3
0.5°	23729.7
1°	23199.4
1.5°	22176.9
2°	21032.0
2.5°	19520.0
3°	17839.4
3.5°	16213.2
4°	14459.2
4.5°	12843.8
5°	11307.3
5.5°	9915.0
6°	8587.9
6.5°	7421.3
7°	6322.6
7.5°	5384.4
8°	4552.3
8.5°	3823.5
9°	3192.6
9.5°	2711.3
10°	2292.5
12.5°	1093.2
15°	617.3
17.5°	375.3
20°	242.0
22.5°	168.6
25°	125.1
27.5°	92.5
30°	70.7
32.5°	54.4
35°	43.5
37.5°	32.6
40°	27.2
42.5°	21.8
45°	16.3
47.5°	10.9
50°	8.2
52.5°	5.4
55°	5.4
57.5°	2.7
60°	2.7
62.5°	2.7
65°	0.0



TEST NUMBER: P777905

CATALOG NUMBER: LERS4D10D010-EC4DR100210IC9035-4LBS1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.0
70°		0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)