

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840336

Luminaire Tested: **LDS4C20D010 EU4209050 4LBPSSQMB**

Issue Date: 8/24/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P840336
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C20D010 EU4209050 4LBSSQMB
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBSSQ TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1621.0 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P840336

CATALOG NUMBER: LDS4C20D010 EU4209050 4LBPSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P840336

CATALOG NUMBER: LDS4C20D010 EU4209050 4LBPSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82131
5°	81845
10°	80949
15°	79555
20°	77771
25°	75696
30°	73312
35°	70486
40°	66934
45°	60846
50°	50242
55°	36992
60°	25106
65°	14703
70°	5812
75°	1305
80°	1723
85°	2878



TEST NUMBER: P840336

CATALOG NUMBER: LDS4C20D010 EU4209050 4LBPSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.1	4.9
10°-20°	224.3	13.8
20°-30°	327.1	20.2
30°-40°	373.4	23.0
40°-50°	339.4	20.9
50°-60°	200.2	12.4
60°-70°	67.1	4.1
70°-80°	7.0	0.4
80°-90°	2.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	631.4	39.0
0°-40°	1004.8	62.0
0°-60°	1544.4	95.3
0°-90°	1621.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1621.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	851	
5°	845	80
15°	796	224
25°	711	327
35°	598	373
45°	446	339
55°	220	200
65°	64	67
75°	4	7
85°	3	2
90°	0	



TEST NUMBER: P840336

CATALOG NUMBER: LDS4C20D010 EU4209050 4LBPSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	851.2
2.5°	849.8
5°	845.0
7.5°	837.1
10°	826.2
12.5°	812.2
15°	796.4
17.5°	778.0
20°	757.4
22.5°	735.1
25°	711.0
27.5°	684.7
30°	658.0
32.5°	628.6
35°	598.4
37.5°	565.5
40°	531.4
42.5°	491.5
45°	445.9
47.5°	393.4
50°	334.7
52.5°	276.0
55°	219.9
57.5°	172.2
60°	130.1
62.5°	94.2
65°	64.4
67.5°	39.4
70°	20.6
72.5°	7.9
75°	3.5
77.5°	3.5
80°	3.1
82.5°	2.6
85°	2.6
87.5°	2.2
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)