

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P777952

Luminaire Tested: LERS4D10D010-EC4DR200210IC9035-4LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P777952  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LERS4D10D010-EC4DR200210IC9035-4LBS1B  
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1101.2 lumens  
Efficiency: N/A  
Efficacy: 94.1 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P777952  
CATALOG NUMBER: LERS4D10D010-EC4DR200210IC9035-4LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P777952

CATALOG NUMBER: LERS4D10D010-EC4DR200210IC9035-4LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |     |  |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  |   |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |     |  |  |  |  |  |  | 10 |  |  |  |  |  |  |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    | 100 |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 1   | 115 | 113 | 111 | 109 | 113 | 111 | 109 | 108 | 107 | 106 | 104 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 97 | 98 | 97  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 2   | 111 | 108 | 105 | 102 | 109 | 106 | 104 | 101 | 103 | 101 | 99  | 100 | 99  | 97  | 98  | 96  | 95  | 94  | 98 | 96 | 95  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 3   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 96  | 100 | 97  | 95  | 97  | 95  | 93  | 95  | 93  | 92  | 91  | 95 | 93 | 92  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 4   | 105 | 99  | 96  | 93  | 103 | 98  | 95  | 92  | 96  | 93  | 91  | 95  | 92  | 90  | 93  | 91  | 89  | 88  | 93 | 91 | 89  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 5   | 102 | 96  | 92  | 89  | 100 | 95  | 91  | 89  | 94  | 90  | 88  | 92  | 89  | 87  | 91  | 88  | 86  | 85  | 91 | 88 | 86  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 6   | 99  | 93  | 89  | 86  | 98  | 92  | 88  | 86  | 91  | 87  | 85  | 90  | 87  | 84  | 88  | 86  | 84  | 83  | 88 | 86 | 84  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 7   | 96  | 90  | 86  | 83  | 95  | 89  | 86  | 83  | 88  | 85  | 82  | 87  | 84  | 82  | 86  | 84  | 82  | 81  | 86 | 84 | 82  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 8   | 94  | 87  | 83  | 81  | 93  | 87  | 83  | 80  | 86  | 83  | 80  | 85  | 82  | 80  | 84  | 82  | 80  | 79  | 84 | 82 | 80  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 9   | 91  | 85  | 81  | 78  | 91  | 85  | 81  | 78  | 84  | 80  | 78  | 83  | 80  | 78  | 82  | 80  | 78  | 77  | 82 | 80 | 78  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 10  | 89  | 83  | 79  | 76  | 88  | 82  | 79  | 76  | 82  | 78  | 76  | 81  | 78  | 76  | 81  | 78  | 76  | 75  | 81 | 78 | 76  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 684825 |
| 5°  | 617850 |
| 10° | 346774 |
| 15° | 176267 |
| 20° | 74636  |
| 25° | 34455  |
| 30° | 18243  |
| 35° | 9830   |
| 40° | 5249   |
| 45° | 3106   |
| 50° | 1802   |
| 55° | 952    |
| 60° | 612    |
| 65° | 440    |
| 70° | 192    |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3106 cd/sqm



TEST NUMBER: P777952

CATALOG NUMBER: LERS4D10D010-EC4DR200210IC9035-4LBS1B

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 446.3  | 40.5      |
| 10°-20°   | 439.4  | 39.9      |
| 20°-30°   | 143.6  | 13.0      |
| 30°-40°   | 48.9   | 4.4       |
| 40°-50°   | 16.4   | 1.5       |
| 50°-60°   | 4.9    | 0.4       |
| 60°-70°   | 1.6    | 0.1       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1029.2 | 93.5      |
| 0°-40°    | 1078.1 | 97.9      |
| 0°-60°    | 1099.5 | 99.8      |
| 0°-90°    | 1101.2 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1101.2 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 6268 |      |
| 5°  | 5633 | 446  |
| 15° | 1558 | 439  |
| 25° | 286  | 144  |
| 35° | 74   | 49   |
| 45° | 20   | 16   |
| 55° | 5    | 5    |
| 65° | 2    | 2    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P777952

CATALOG NUMBER: LERS4D10D010-EC4DR200210IC9035-4LBS1B

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 6267.8 |
| 0.5°  | 6267.8 |
| 1°    | 6260.0 |
| 1.5°  | 6244.4 |
| 2°    | 6215.9 |
| 2.5°  | 6178.0 |
| 3°    | 6124.4 |
| 3.5°  | 6049.6 |
| 4°    | 5938.5 |
| 4.5°  | 5803.5 |
| 5°    | 5633.3 |
| 5.5°  | 5409.4 |
| 6°    | 5180.0 |
| 6.5°  | 4917.2 |
| 7°    | 4659.9 |
| 7.5°  | 4358.5 |
| 8°    | 4089.5 |
| 8.5°  | 3818.8 |
| 9°    | 3568.7 |
| 9.5°  | 3339.3 |
| 10°   | 3125.6 |
| 12.5° | 2244.3 |
| 15°   | 1558.3 |
| 17.5° | 1018.0 |
| 20°   | 641.9  |
| 22.5° | 415.8  |
| 25°   | 285.8  |
| 27.5° | 200.9  |
| 30°   | 144.6  |
| 32.5° | 103.8  |
| 35°   | 73.7   |
| 37.5° | 51.3   |
| 40°   | 36.8   |
| 42.5° | 26.8   |
| 45°   | 20.1   |
| 47.5° | 15.6   |
| 50°   | 10.6   |
| 52.5° | 6.7    |
| 55°   | 5.0    |
| 57.5° | 3.9    |
| 60°   | 2.8    |
| 62.5° | 2.2    |
| 65°   | 1.7    |



TEST NUMBER: P777952

CATALOG NUMBER: LERS4D10D010-EC4DR200210IC9035-4LBS1B

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





|       |  |     |
|-------|--|-----|
| 67.5° |  | 1.1 |
| 70°   |  | 0.6 |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)