

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840432

Luminaire Tested: **LDS4C70D010 EU4709035 4LBPSSQMB**

Issue Date: 8/24/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P840432  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C70D010 EU4709035 4LBSSQMB  
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 4LBSSQ TRIM WITH MB FINISH  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5577.0 lumens  
Efficiency: N/A  
Efficacy: 71.5 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 78  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P840432

CATALOG NUMBER: LDS4C70D010 EU4709035 4LBPSSQMB

### Luminous Intensity Polar Plot





TEST NUMBER: P840432

CATALOG NUMBER: LDS4C70D010 EU4709035 4LBPSSQMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	282558
5°	281594
10°	278501
15°	273706
20°	267577
25°	260421
30°	252212
35°	242509
40°	230275
45°	209364
50°	172852
55°	127278
60°	86377
65°	50594
70°	19974
75°	4511
80°	5890
85°	9964



TEST NUMBER: P840432

CATALOG NUMBER: LDS4C70D010 EU4709035 4LBPSSQMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	275.5	4.9
10°-20°	771.5	13.8
20°-30°	1125.4	20.2
30°-40°	1284.6	23.0
40°-50°	1167.8	20.9
50°-60°	688.8	12.4
60°-70°	231.0	4.1
70°-80°	24.1	0.4
80°-90°	8.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2172.4	39.0
0°-40°	3456.9	62.0
0°-60°	5313.5	95.3
0°-90°	5577.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5577.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2928	
5°	2907	275
15°	2740	772
25°	2446	1125
35°	2059	1285
45°	1534	1168
55°	757	689
65°	222	231
75°	12	24
85°	9	8
90°	0	



TEST NUMBER: P840432

CATALOG NUMBER: LDS4C70D010 EU4709035 4LBPSSQMB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2928.4
2.5°	2923.9
5°	2907.3
7.5°	2880.2
10°	2842.5
12.5°	2794.2
15°	2740.0
17.5°	2676.7
20°	2605.9
22.5°	2529.0
25°	2446.1
27.5°	2355.7
30°	2263.7
32.5°	2162.8
35°	2058.8
37.5°	1945.7
40°	1828.2
42.5°	1691.0
45°	1534.3
47.5°	1353.4
50°	1151.5
52.5°	949.5
55°	756.6
57.5°	592.3
60°	447.6
62.5°	324.0
65°	221.6
67.5°	135.6
70°	70.8
72.5°	27.1
75°	12.1
77.5°	12.1
80°	10.6
82.5°	9.0
85°	9.0
87.5°	7.5
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)