

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840433

Luminaire Tested: **LDS4C70D010 EU4709035 4LBPSSQMMS**

Issue Date: 8/24/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P840433
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C70D010 EU4709035 4LBPSSQMMS
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBPSSQ TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5703.0 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P840433

CATALOG NUMBER: LDS4C70D010 EU4709035 4LBPSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P840433

CATALOG NUMBER: LDS4C70D010 EU4709035 4LBPSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	288936
5°	287957
10°	284791
15°	279889
20°	273615
25°	266308
30°	257916
35°	247986
40°	235477
45°	214086
50°	176755
55°	130154
60°	88326
65°	51736
70°	20425
75°	4585
80°	6001
85°	10185



TEST NUMBER: P840433

CATALOG NUMBER: LDS4C70D010 EU4709035 4LBPSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	281.7	4.9
10°-20°	789.0	13.8
20°-30°	1150.8	20.2
30°-40°	1313.6	23.0
40°-50°	1194.2	20.9
50°-60°	704.3	12.4
60°-70°	236.2	4.1
70°-80°	24.6	0.4
80°-90°	8.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2221.4	39.0
0°-40°	3535.0	62.0
0°-60°	5433.5	95.3
0°-90°	5703.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5703.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2994	
5°	2973	282
15°	2802	789
25°	2501	1151
35°	2105	1314
45°	1569	1194
55°	774	704
65°	227	236
75°	12	25
85°	9	9
90°	0	



TEST NUMBER: P840433

CATALOG NUMBER: LDS4C70D010 EU4709035 4LBPSSQMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2994.5
2.5°	2989.9
5°	2973.0
7.5°	2945.2
10°	2906.7
12.5°	2857.4
15°	2801.9
17.5°	2737.2
20°	2664.7
22.5°	2586.1
25°	2501.4
27.5°	2408.9
30°	2314.9
32.5°	2211.6
35°	2105.3
37.5°	1989.7
40°	1869.5
42.5°	1729.2
45°	1568.9
47.5°	1384.0
50°	1177.5
52.5°	971.0
55°	773.7
57.5°	605.7
60°	457.7
62.5°	331.4
65°	226.6
67.5°	138.7
70°	72.4
72.5°	27.7
75°	12.3
77.5°	12.3
80°	10.8
82.5°	9.2
85°	9.2
87.5°	7.7
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)