

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P778157

Luminaire Tested: LERS4D10D010-EC4DR650210IC9024-4LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P778157  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LERS4D10D010-EC4DR650210IC9024-4LBS1H  
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 804.1 lumens  
Efficiency: N/A  
Efficacy: 68.7 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P778157

CATALOG NUMBER: LERS4D10D010-EC4DR650210IC9024-4LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P778157

CATALOG NUMBER: LERS4D10D010-EC4DR650210IC9024-4LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	89	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	42647
5°	42540
10°	42498
15°	41188
20°	37503
25°	32678
30°	27178
35°	21539
40°	15546
45°	9821
50°	5115
55°	2719
60°	1425
65°	788
70°	324
75°	361
80°	235
85°	201

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9821 cd/sqm



TEST NUMBER: P778157

CATALOG NUMBER: LERS4D10D010-EC4DR650210IC9024-4LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.1	8.6
10°-20°	189.1	23.5
20°-30°	231.1	28.7
30°-40°	187.6	23.3
40°-50°	93.4	11.6
50°-60°	26.0	3.2
60°-70°	5.9	0.7
70°-80°	1.5	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	489.3	60.8
0°-40°	676.8	84.2
0°-60°	796.3	99.0
0°-90°	804.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	804.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	730	
5°	726	69
15°	681	189
25°	507	231
35°	302	188
45°	119	93
55°	27	26
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P778157

CATALOG NUMBER: LERS4D10D010-EC4DR650210IC9024-4LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	730.2
2.5°	729.7
5°	725.6
7.5°	723.2
10°	716.6
12.5°	703.4
15°	681.2
17.5°	646.7
20°	603.4
22.5°	556.6
25°	507.1
27.5°	454.2
30°	403.0
32.5°	352.5
35°	302.1
37.5°	251.8
40°	203.9
42.5°	159.0
45°	118.9
47.5°	82.8
50°	56.3
52.5°	38.8
55°	26.7
57.5°	18.0
60°	12.2
62.5°	8.5
65°	5.7
67.5°	2.9
70°	1.9
72.5°	1.8
75°	1.6
77.5°	1.1
80°	0.7
82.5°	0.5
85°	0.3
87.5°	0.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)