

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170600

Luminaire Tested: **LDA4A13840D010TE LAR15SP 4LFC1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P170600  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26141)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA4A13840D010TE LAR15SP 4LFC1  
Description: PORTFOLIO 4" Flat Cone, Self-flange Trim Ring, 15° Spot Optic, at 0° tilt  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1581.2 lumens  
Efficiency: N/A  
Efficacy: 71.0 lumens/watt  
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.36  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 22.27  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P170600

CATALOG NUMBER: LDA4A13840D010TE LAR15SP 4LFC1

### Luminous Intensity Polar Plot





TEST NUMBER: P170600

CATALOG NUMBER: LDA4A13840D010TE LAR15SP 4LFC1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 115 | 113 | 112 | 110 | 113 | 111 | 110 | 108 | 107 | 106 | 105 | 104 | 103 | 102 | 100 | 100 | 99  | 97  |
| 2   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 102 | 104 | 102 | 100 | 101 | 99  | 98  | 98  | 97  | 96  | 95  |
| 3   | 109 | 104 | 101 | 98  | 107 | 103 | 100 | 98  | 101 | 98  | 96  | 98  | 96  | 95  | 96  | 95  | 93  | 92  |
| 4   | 106 | 101 | 97  | 94  | 104 | 100 | 97  | 94  | 98  | 95  | 93  | 96  | 94  | 92  | 94  | 92  | 91  | 90  |
| 5   | 103 | 98  | 94  | 91  | 102 | 97  | 93  | 91  | 95  | 92  | 90  | 94  | 91  | 89  | 92  | 90  | 89  | 88  |
| 6   | 100 | 95  | 91  | 88  | 99  | 94  | 91  | 88  | 93  | 90  | 87  | 92  | 89  | 87  | 91  | 88  | 86  | 85  |
| 7   | 98  | 92  | 88  | 86  | 97  | 92  | 88  | 86  | 91  | 87  | 85  | 90  | 87  | 85  | 89  | 86  | 84  | 83  |
| 8   | 96  | 90  | 86  | 83  | 95  | 89  | 86  | 83  | 88  | 85  | 83  | 88  | 85  | 83  | 87  | 84  | 82  | 81  |
| 9   | 94  | 88  | 84  | 81  | 93  | 87  | 84  | 81  | 86  | 83  | 81  | 86  | 83  | 81  | 85  | 82  | 81  | 80  |
| 10  | 91  | 85  | 82  | 79  | 91  | 85  | 82  | 79  | 84  | 81  | 79  | 84  | 81  | 79  | 83  | 81  | 79  | 78  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1235393 |
| 5°  | 1044556 |
| 10° | 572435  |
| 15° | 312474  |
| 20° | 174079  |
| 25° | 40217   |
| 30° | 7777    |
| 35° | 2244    |
| 40° | 805     |
| 45° | 297     |
| 50° | 0       |
| 55° | 0       |
| 60° | 0       |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P170600

CATALOG NUMBER: LDA4A13840D010TE LAR15SP 4LFC1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 664.3  | 42.0      |
| 10°-20°   | 695.0  | 44.0      |
| 20°-30°   | 208.4  | 13.2      |
| 30°-40°   | 12.1   | 0.8       |
| 40°-50°   | 1.4    | 0.1       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1567.7 | 99.1      |
| 0°-40°    | 1579.8 | 99.9      |
| 0°-60°    | 1581.2 | 100.0     |
| 0°-90°    | 1581.2 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1581.2 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 10016 |      |
| 5°  | 8436  | 664  |
| 15° | 2447  | 695  |
| 25° | 296   | 208  |
| 35° | 15    | 12   |
| 45° | 2     | 1    |
| 55° | 0     | 0    |
| 65° | 0     | 0    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P170600

CATALOG NUMBER: LDA4A13840D010TE LAR15SP 4LFC1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 10015.7 |
| 1°    | 9917.2  |
| 2°    | 9739.2  |
| 3°    | 9500.8  |
| 4°    | 9088.6  |
| 5°    | 8436.3  |
| 6°    | 7629.1  |
| 7°    | 6750.8  |
| 8°    | 5934.6  |
| 9°    | 5188.7  |
| 10°   | 4570.4  |
| 11°   | 4034.8  |
| 12°   | 3558.8  |
| 13°   | 3147.3  |
| 14°   | 2779.0  |
| 15°   | 2447.0  |
| 17.5° | 1778.1  |
| 20°   | 1326.2  |
| 22.5° | 874.2   |
| 25°   | 295.5   |
| 27.5° | 102.6   |
| 30°   | 54.6    |
| 32.5° | 27.3    |
| 35°   | 14.9    |
| 37.5° | 8.3     |
| 40°   | 5.0     |
| 42.5° | 2.5     |
| 45°   | 1.7     |
| 47.5° | 0.8     |
| 50°   | 0.0     |
| 52.5° | 0.0     |
| 55°   | 0.0     |
| 57.5° | 0.0     |
| 60°   | 0.0     |
| 62.5° | 0.0     |
| 65°   | 0.0     |
| 67.5° | 0.0     |
| 70°   | 0.0     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |



TEST NUMBER: P170600

CATALOG NUMBER: LDA4A13840D010TE LAR15SP 4LFC1

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







|       |  |     |
|-------|--|-----|
| 85°   |  | 0.0 |
| 87.5° |  | 0.0 |



(END OF REPORT)