

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170169

Luminaire Tested: **LDA4A18927D010TE LAR15SP 4LPIN**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170169
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A18927D010TE LAR15SP 4LPIN
Description: PORTFOLIO 4" White Pinhole with Black Oculus, Self-flanged, 15° Spot
Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 520.8 lumens
Efficiency: N/A
Efficacy: 17.9 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.31
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 29.12
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170169
CATALOG NUMBER: LDA4A18927D010TE LAR15SP 4LPIN

Luminous Intensity Polar Plot





TEST NUMBER: P170169

CATALOG NUMBER: LDA4A18927D010TE LAR15SP 4LPIN

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 116 | 114 | 113 | 111 | 114 | 112 | 111 | 109 | 108 | 107 | 106 | 105 | 104 | 103 | 101 | 101 | 100 | 98 | 98 | 98 | 98 |
| 2 | 113 | 110 | 108 | 106 | 111 | 109 | 107 | 105 | 106 | 104 | 103 | 103 | 102 | 100 | 100 | 99 | 98 | 97 | 97 | 97 | 97 |
| 3 | 111 | 107 | 104 | 102 | 109 | 106 | 103 | 101 | 103 | 101 | 100 | 101 | 100 | 98 | 99 | 98 | 97 | 96 | 96 | 96 | 96 |
| 4 | 109 | 104 | 101 | 99 | 107 | 103 | 101 | 99 | 102 | 99 | 97 | 100 | 98 | 96 | 98 | 97 | 95 | 94 | 94 | 94 | 94 |
| 5 | 107 | 102 | 99 | 97 | 105 | 101 | 98 | 96 | 100 | 97 | 96 | 98 | 96 | 95 | 97 | 95 | 94 | 93 | 93 | 93 | 93 |
| 6 | 105 | 100 | 97 | 95 | 104 | 99 | 97 | 94 | 98 | 96 | 94 | 97 | 95 | 93 | 96 | 94 | 93 | 92 | 92 | 92 | 92 |
| 7 | 103 | 98 | 95 | 93 | 102 | 98 | 95 | 93 | 97 | 94 | 92 | 96 | 94 | 92 | 95 | 93 | 92 | 91 | 91 | 91 | 91 |
| 8 | 101 | 97 | 94 | 92 | 101 | 96 | 93 | 91 | 95 | 93 | 91 | 95 | 92 | 91 | 94 | 92 | 91 | 90 | 90 | 90 | 90 |
| 9 | 100 | 95 | 92 | 90 | 99 | 95 | 92 | 90 | 94 | 92 | 90 | 93 | 91 | 90 | 93 | 91 | 89 | 89 | 89 | 89 | 89 |
| 10 | 98 | 94 | 91 | 89 | 98 | 93 | 91 | 89 | 93 | 90 | 89 | 92 | 90 | 89 | 92 | 90 | 88 | 88 | 88 | 88 | 88 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 567600 |
| 5° | 510447 |
| 10° | 274482 |
| 15° | 69110 |
| 20° | 9267 |
| 25° | 1824 |
| 30° | 498 |
| 35° | 105 |
| 40° | 113 |
| 45° | 0 |
| 50° | 0 |
| 55° | 0 |
| 60° | 0 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P170169

CATALOG NUMBER: LDA4A18927D010TE LAR15SP 4LPIN

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 331.3 | 63.6 |
| 10°-20° | 179.5 | 34.5 |
| 20°-30° | 9.1 | 1.8 |
| 30°-40° | 0.7 | 0.1 |
| 40°-50° | 0.1 | 0.0 |
| 50°-60° | 0.0 | 0.0 |
| 60°-70° | 0.0 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 520.0 | 99.8 |
| 0°-40° | 520.7 | 100.0 |
| 0°-60° | 520.8 | 100.0 |
| 0°-90° | 520.8 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 520.8 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4602 | |
| 5° | 4123 | 331 |
| 15° | 541 | 180 |
| 25° | 13 | 9 |
| 35° | 1 | 1 |
| 45° | 0 | 0 |
| 55° | 0 | 0 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P170169

CATALOG NUMBER: LDA4A18927D010TE LAR15SP 4LPIN

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 4601.7 |
| 1° | 4573.5 |
| 2° | 4521.3 |
| 3° | 4437.3 |
| 4° | 4321.6 |
| 5° | 4122.6 |
| 6° | 3858.7 |
| 7° | 3532.8 |
| 8° | 3139.8 |
| 9° | 2677.6 |
| 10° | 2191.5 |
| 11° | 1723.0 |
| 12° | 1311.6 |
| 13° | 985.7 |
| 14° | 741.5 |
| 15° | 541.2 |
| 17.5° | 199.0 |
| 20° | 70.6 |
| 22.5° | 28.9 |
| 25° | 13.4 |
| 27.5° | 6.4 |
| 30° | 3.5 |
| 32.5° | 1.4 |
| 35° | 0.7 |
| 37.5° | 0.7 |
| 40° | 0.7 |
| 42.5° | 0.0 |
| 45° | 0.0 |
| 47.5° | 0.0 |
| 50° | 0.0 |
| 52.5° | 0.0 |
| 55° | 0.0 |
| 57.5° | 0.0 |
| 60° | 0.0 |
| 62.5° | 0.0 |
| 65° | 0.0 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |



TEST NUMBER: P170169

CATALOG NUMBER: LDA4A18927D010TE LAR15SP 4LPIN

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|-----|
| 85° | | 0.0 |
| 87.5° | | 0.0 |



(END OF REPORT)