

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P778255

Luminaire Tested: LERS4D15D010-EC4DR2015309024-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P778255
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS4D15D010-EC4DR2015309024-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1241.5 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P778255
CATALOG NUMBER: LERS4D15D010-EC4DR2015309024-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P778255

CATALOG NUMBER: LERS4D15D010-EC4DR2015309024-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	97																
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	94																
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	91																
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	93	89																
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	91	86																
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	88	84																
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	86	82																
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	84	80																
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	82	78																
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	81	76																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	772047
5°	696533
10°	390930
15°	198721
20°	84135
25°	38843
30°	20565
35°	11084
40°	5919
45°	3508
50°	2040
55°	1086
60°	677
65°	491
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3508 cd/sqm



TEST NUMBER: P778255

CATALOG NUMBER: LERS4D15D010-EC4DR2015309024-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	503.1	40.5
10°-20°	495.4	39.9
20°-30°	161.8	13.0
30°-40°	55.1	4.4
40°-50°	18.5	1.5
50°-60°	5.6	0.5
60°-70°	1.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1160.3	93.5
0°-40°	1215.4	97.9
0°-60°	1239.6	99.8
0°-90°	1241.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1241.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7066	
5°	6351	503
15°	1757	495
25°	322	162
35°	83	55
45°	23	19
55°	6	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P778255

CATALOG NUMBER: LERS4D15D010-EC4DR2015309024-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7066.1
0.5°	7066.1
1°	7057.3
1.5°	7039.7
2°	7007.6
2.5°	6964.8
3°	6904.4
3.5°	6820.1
4°	6694.9
4.5°	6542.6
5°	6350.7
5.5°	6098.4
6°	5839.8
6.5°	5543.4
7°	5253.4
7.5°	4913.6
8°	4610.3
8.5°	4305.1
9°	4023.2
9.5°	3764.6
10°	3523.6
12.5°	2530.1
15°	1756.8
17.5°	1147.7
20°	723.6
22.5°	468.8
25°	322.2
27.5°	226.5
30°	163.0
32.5°	117.0
35°	83.1
37.5°	57.9
40°	41.5
42.5°	30.2
45°	22.7
47.5°	17.6
50°	12.0
52.5°	7.6
55°	5.7
57.5°	4.4
60°	3.1
62.5°	2.5
65°	1.9



TEST NUMBER: P778255
CATALOG NUMBER: LERS4D15D010-EC4DR2015309024-4LBS1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		1.3
70°		0.6

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)