

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170426

Luminaire Tested: **LDA4A18930D010TE LAR25NF 4LA1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P170426  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25629)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA4A18930D010TE LAR25NF 4LA1  
Description: PORTFOLIO 4" Adjustable Reflector, Self-flange Trim Ring, 25° Narrow Flood Optic, at 0° tilt  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1408.8 lumens  
Efficiency: N/A  
Efficacy: 48.4 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.45  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 29.12  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P170426

CATALOG NUMBER: LDA4A18930D010TE LAR25NF 4LA1

### Luminous Intensity Polar Plot





TEST NUMBER: P170426

CATALOG NUMBER: LDA4A18930D010TE LAR25NF 4LA1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 115 | 113 | 111 | 110 | 113 | 111 | 109 | 108 | 107 | 106 | 105 | 103 | 102 | 101 | 100 | 99  | 99  | 97  | 97  | 97  | 97  |
| 2   | 112 | 108 | 105 | 103 | 109 | 106 | 104 | 102 | 103 | 101 | 99  | 100 | 99  | 97  | 98  | 96  | 95  | 94  | 94  | 94  | 94  |
| 3   | 108 | 104 | 100 | 97  | 106 | 102 | 99  | 97  | 100 | 97  | 95  | 98  | 96  | 94  | 96  | 94  | 92  | 91  | 91  | 91  | 91  |
| 4   | 105 | 100 | 96  | 93  | 103 | 99  | 95  | 93  | 97  | 94  | 92  | 95  | 93  | 91  | 93  | 91  | 90  | 88  | 88  | 88  | 88  |
| 5   | 102 | 96  | 92  | 89  | 101 | 95  | 92  | 89  | 94  | 91  | 88  | 92  | 90  | 88  | 91  | 89  | 87  | 86  | 86  | 86  | 86  |
| 6   | 99  | 93  | 89  | 86  | 98  | 93  | 89  | 86  | 91  | 88  | 85  | 90  | 87  | 85  | 89  | 86  | 84  | 83  | 83  | 83  | 83  |
| 7   | 97  | 90  | 86  | 83  | 95  | 90  | 86  | 83  | 89  | 85  | 83  | 88  | 85  | 83  | 87  | 84  | 82  | 81  | 81  | 81  | 81  |
| 8   | 94  | 88  | 84  | 81  | 93  | 87  | 83  | 81  | 86  | 83  | 81  | 85  | 82  | 80  | 85  | 82  | 80  | 79  | 79  | 79  | 79  |
| 9   | 92  | 85  | 81  | 79  | 91  | 85  | 81  | 79  | 84  | 81  | 78  | 83  | 80  | 78  | 83  | 80  | 78  | 77  | 77  | 77  | 77  |
| 10  | 89  | 83  | 79  | 76  | 89  | 83  | 79  | 76  | 82  | 79  | 76  | 81  | 78  | 76  | 81  | 78  | 76  | 75  | 75  | 75  | 75  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 785046 |
| 5°  | 688161 |
| 10° | 513268 |
| 15° | 326508 |
| 20° | 173147 |
| 25° | 39073  |
| 30° | 9386   |
| 35° | 2695   |
| 40° | 918    |
| 45° | 279    |
| 50° | 154    |
| 55° | 172    |
| 60° | 197    |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P170426

CATALOG NUMBER: LDA4A18930D010TE LAR25NF 4LA1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 486.2  | 34.5      |
| 10°-20°   | 698.5  | 49.6      |
| 20°-30°   | 206.6  | 14.7      |
| 30°-40°   | 14.7   | 1.0       |
| 40°-50°   | 1.7    | 0.1       |
| 50°-60°   | 0.7    | 0.1       |
| 60°-70°   | 0.5    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1391.3 | 98.8      |
| 0°-40°    | 1406.0 | 99.8      |
| 0°-60°    | 1408.4 | 100.0     |
| 0°-90°    | 1408.8 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1408.8 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 6365 |      |
| 5°  | 5558 | 486  |
| 15° | 2557 | 699  |
| 25° | 287  | 207  |
| 35° | 18   | 15   |
| 45° | 2    | 2    |
| 55° | 1    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P170426

CATALOG NUMBER: LDA4A18930D010TE LAR25NF 4LA1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 6364.6 |
| 2.5°  | 6030.4 |
| 5°    | 5557.9 |
| 7.5°  | 4943.8 |
| 10°   | 4098.0 |
| 12.5° | 3302.7 |
| 15°   | 2556.9 |
| 17.5° | 1863.2 |
| 20°   | 1319.1 |
| 22.5° | 835.2  |
| 25°   | 287.1  |
| 27.5° | 125.2  |
| 30°   | 65.9   |
| 32.5° | 33.3   |
| 35°   | 17.9   |
| 37.5° | 10.6   |
| 40°   | 5.7    |
| 42.5° | 3.3    |
| 45°   | 1.6    |
| 47.5° | 0.8    |
| 50°   | 0.8    |
| 52.5° | 0.8    |
| 55°   | 0.8    |
| 57.5° | 0.8    |
| 60°   | 0.8    |
| 62.5° | 0.8    |
| 65°   | 0.0    |
| 67.5° | 0.8    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)