

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170523

Luminaire Tested: **LDA4A18935D010TE LAR25NF 4LAL1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170523
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26145)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A18935D010TE LAR25NF 4LAL1
Description: PORTFOLIO 4" Lensed Adjustable, Self-flange Trim Ring, 25° Narrow Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1546.8 lumens
Efficiency: N/A
Efficacy: 53.1 lumens/watt
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.45
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 29.12
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170523

CATALOG NUMBER: LDA4A18935D010TE LAR25NF 4LAL1

Luminous Intensity Polar Plot





TEST NUMBER: P170523

CATALOG NUMBER: LDA4A18935D010TE LAR25NF 4LAL1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	103	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	91
4	105	100	96	93	103	98	95	92	97	94	91	95	92	90	93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83
7	96	90	86	83	95	89	85	83	88	85	82	87	84	82	86	84	82	81
8	94	87	83	80	93	87	83	80	86	82	80	85	82	80	84	81	79	78
9	91	85	81	78	90	84	80	78	83	80	78	83	80	77	82	79	77	76
10	89	82	78	76	88	82	78	76	81	78	76	81	78	75	80	77	75	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	899523
5°	725554
10°	545357
15°	362480
20°	194425
25°	49199
30°	11679
35°	3825
40°	1578
45°	715
50°	307
55°	172
60°	197
65°	233
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170523

CATALOG NUMBER: LDA4A18935D010TE LAR25NF 4LAL1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	515.1	33.3
10°-20°	767.6	49.6
20°-30°	239.8	15.5
30°-40°	19.7	1.3
40°-50°	3.4	0.2
50°-60°	0.8	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1522.4	98.4
0°-40°	1542.1	99.7
0°-60°	1546.3	100.0
0°-90°	1546.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1546.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7293	
5°	5860	515
15°	2839	768
25°	362	240
35°	25	20
45°	4	3
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170523

CATALOG NUMBER: LDA4A18935D010TE LAR25NF 4LAL1

CANDELA DISTRIBUTION (FULL):

	0°
0°	7292.7
1°	7148.5
2°	6800.1
3°	6434.5
4°	6132.9
5°	5859.9
6°	5605.0
7°	5330.4
8°	5018.9
9°	4696.0
10°	4354.2
11°	4027.1
12°	3719.7
13°	3423.0
14°	3129.6
15°	2838.6
17.5°	2116.4
20°	1481.2
22.5°	959.9
25°	361.5
27.5°	144.3
30°	82.0
32.5°	43.4
35°	25.4
37.5°	15.6
40°	9.8
42.5°	5.7
45°	4.1
47.5°	2.5
50°	1.6
52.5°	0.8
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P170523

CATALOG NUMBER: LDA4A18935D010TE LAR25NF 4LAL1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)