

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170428

Luminaire Tested: **LDA4A18940D010TE LAR25NF 4LA1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170428
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25629)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A18940D010TE LAR25NF 4LA1
Description: PORTFOLIO 4" Adjustable Reflector, Self-flange Trim Ring, 25° Narrow Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1524.5 lumens
Efficiency: N/A
Efficacy: 52.4 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.45
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 29.12
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170428

CATALOG NUMBER: LDA4A18940D010TE LAR25NF 4LA1

Luminous Intensity Polar Plot





TEST NUMBER: P170428

CATALOG NUMBER: LDA4A18940D010TE LAR25NF 4LA1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97	97	99	97																
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	95	94	94	95	94																
3	108	104	100	97	106	102	99	97	100	97	95	98	96	94	96	94	92	91	92	91	91																
4	105	100	96	93	103	99	95	93	97	94	92	95	93	91	93	91	90	88	90	89	88																
5	102	96	92	89	101	95	92	89	94	91	88	92	90	88	91	89	87	86	87	86	86																
6	99	93	89	86	98	93	89	86	91	88	85	90	87	85	89	86	84	83	85	84	83																
7	97	90	86	83	95	90	86	83	89	85	83	88	85	83	87	84	82	81	84	83	81																
8	94	88	84	81	93	87	83	81	86	83	81	85	82	80	85	82	80	79	82	80	79																
9	92	85	81	79	91	85	81	79	84	81	78	83	80	78	83	80	78	77	78	78	77																
10	89	83	79	76	89	83	79	76	82	79	76	81	78	76	81	78	76	75	76	76	75																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	849420
5°	744585
10°	555364
15°	353286
20°	187350
25°	42272
30°	10155
35°	2921
40°	998
45°	314
50°	173
55°	194
60°	222
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170428

CATALOG NUMBER: LDA4A18940D010TE LAR25NF 4LA1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	526.1	34.5
10°-20°	755.8	49.6
20°-30°	223.5	14.7
30°-40°	15.9	1.0
40°-50°	1.8	0.1
50°-60°	0.8	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1505.4	98.7
0°-40°	1521.3	99.8
0°-60°	1523.9	100.0
0°-90°	1524.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1524.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6886	
5°	6014	526
15°	2767	756
25°	311	224
35°	19	16
45°	2	2
55°	1	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170428

CATALOG NUMBER: LDA4A18940D010TE LAR25NF 4LA1

CANDELA DISTRIBUTION (FULL):

	0°
0°	6886.5
2.5°	6524.8
5°	6013.6
7.5°	5349.2
10°	4434.1
12.5°	3573.5
15°	2766.6
17.5°	2016.0
20°	1427.3
22.5°	903.7
25°	310.6
27.5°	135.5
30°	71.3
32.5°	36.1
35°	19.4
37.5°	11.4
40°	6.2
42.5°	3.5
45°	1.8
47.5°	0.9
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.0
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)