

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170642

Luminaire Tested: **LDA4A28930D010TE LAR25NF 4LFC1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P170642  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26142)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA4A28930D010TE LAR25NF 4LFC1  
Description: PORTFOLIO 4" Flat Cone, Self-flange Trim Ring, 25° Narrow Flood Optic, at 0° tilt  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2636.6 lumens  
Efficiency: N/A  
Efficacy: 59.3 lumens/watt  
Spacing Criteria (0/90/45): 0.46 / 0.46 / 0.47  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 44.49  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P170642

CATALOG NUMBER: LDA4A28930D010TE LAR25NF 4LFC1

### Luminous Intensity Polar Plot





TEST NUMBER: P170642

CATALOG NUMBER: LDA4A28930D010TE LAR25NF 4LFC1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97
2	111	108	105	103	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94	94
3	108	104	100	97	106	102	99	96	100	97	95	98	95	94	95	94	92	91	91	91	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	88	88	88	88
5	102	96	92	89	100	95	92	89	94	91	88	92	89	87	91	89	87	86	86	86	86
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	83	83	83	83
7	96	90	86	83	95	89	86	83	88	85	83	87	84	82	86	84	82	81	81	81	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	79	79	79	79	79
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	76	76	76	76
10	89	82	79	76	88	82	78	76	81	78	76	81	78	76	80	77	75	74	74	74	74

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1364795
5°	1253335
10°	936232
15°	623620
20°	337815
25°	80583
30°	18857
35°	5376
40°	1852
45°	663
50°	249
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170642

CATALOG NUMBER: LDA4A28930D010TE LAR25NF 4LFC1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	877.2	33.3
10°-20°	1322.8	50.2
20°-30°	403.9	15.3
30°-40°	29.2	1.1
40°-50°	3.4	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2603.9	98.8
0°-40°	2633.1	99.9
0°-60°	2636.6	100.0
<b>0°-90°</b>	<b>2636.6</b>	<b>100.0</b>
90°-120°	0.0	0.0
90°-150°	0.0	0.0
<b>90°-180°</b>	<b>0.0</b>	<b>0.0</b>
0°-180°	2636.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11065	
5°	10122	877
15°	4884	1323
25°	592	404
35°	36	29
45°	4	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170642

CATALOG NUMBER: LDA4A28930D010TE LAR25NF 4LFC1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11064.8
1°	10940.0
2°	10760.5
3°	10625.5
4°	10453.6
5°	10122.5
6°	9706.1
7°	9185.3
8°	8647.9
9°	8074.8
10°	7475.0
11°	6903.3
12°	6379.9
13°	5878.2
14°	5394.3
15°	4883.6
17.5°	3668.8
20°	2573.6
22.5°	1605.8
25°	592.1
27.5°	239.4
30°	132.4
32.5°	66.2
35°	35.7
37.5°	20.4
40°	11.5
42.5°	6.4
45°	3.8
47.5°	1.3
50°	1.3
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P170642

CATALOG NUMBER: LDA4A28930D010TE LAR25NF 4LFC1

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)