

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170544

Luminaire Tested: **LDA4A28840D010TE LAR25NF 4LAL1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170544
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26145)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A28840D010TE LAR25NF 4LAL1
Description: PORTFOLIO 4" Lensed Adjustable, Self-flange Trim Ring, 25° Narrow Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3030.4 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.45
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 44.49
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170544

CATALOG NUMBER: LDA4A28840D010TE LAR25NF 4LAL1

Luminous Intensity Polar Plot





TEST NUMBER: P170544

CATALOG NUMBER: LDA4A28840D010TE LAR25NF 4LAL1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97																
2	111	108	105	103	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94	94																
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	91	91	91	91																
4	105	100	96	93	103	98	95	92	97	94	91	95	92	90	93	91	89	88	88	88	88																
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	85	85																
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	83	83																
7	96	90	86	83	95	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81																
8	94	87	83	80	93	87	83	80	86	82	80	85	82	80	84	81	79	78	78	78	78																
9	91	85	81	78	90	84	80	78	83	80	78	83	80	77	82	79	77	76	76	76	76																
10	89	82	78	76	88	82	78	76	81	78	76	81	78	75	80	77	75	74	74	74	74																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1762288
5°	1421454
10°	1068407
15°	710135
20°	380895
25°	96384
30°	22874
35°	7499
40°	3108
45°	1395
50°	614
55°	344
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170544

CATALOG NUMBER: LDA4A28840D010TE LAR25NF 4LAL1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1009.1	33.3
10°-20°	1503.7	49.6
20°-30°	469.8	15.5
30°-40°	38.5	1.3
40°-50°	6.7	0.2
50°-60°	1.6	0.1
60°-70°	1.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2982.6	98.4
0°-40°	3021.1	99.7
0°-60°	3029.4	100.0
0°-90°	3030.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3030.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14287	
5°	11480	###
15°	5561	1504
25°	708	470
35°	50	39
45°	8	7
55°	2	2
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170544

CATALOG NUMBER: LDA4A28840D010TE LAR25NF 4LAL1

CANDELA DISTRIBUTION (FULL):

	0°
0°	14287.4
1°	14004.7
2°	13322.2
3°	12606.0
4°	12015.1
5°	11480.3
6°	10980.9
7°	10442.9
8°	9832.7
9°	9200.0
10°	8530.3
11°	7889.6
12°	7287.4
13°	6706.1
14°	6131.2
15°	5561.1
17.5°	4146.3
20°	2901.8
22.5°	1880.5
25°	708.2
27.5°	282.6
30°	160.6
32.5°	85.1
35°	49.8
37.5°	30.5
40°	19.3
42.5°	11.2
45°	8.0
47.5°	4.8
50°	3.2
52.5°	1.6
55°	1.6
57.5°	1.6
60°	1.6
62.5°	1.6
65°	1.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P170544

CATALOG NUMBER: LDA4A28840D010TE LAR25NF 4LAL1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)