

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170653

Luminaire Tested: **LDA4A09827D010TE LAR35FL 4LFC1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170653
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26143)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A09827D010TE LAR35FL 4LFC1
Description: PORTFOLIO 4" Flat Cone, Self-flange Trim Ring, 35° Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1028.9 lumens
Efficiency: N/A
Efficacy: 74.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.56
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 13.84
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170653

CATALOG NUMBER: LDA4A09827D010TE LAR35FL 4LFC1

Luminous Intensity Polar Plot





TEST NUMBER: P170653

CATALOG NUMBER: LDA4A09827D010TE LAR35FL 4LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96
2	111	107	104	102	109	106	103	101	103	100	99	100	98	96	97	96	94	93
3	107	103	99	96	106	101	98	95	99	96	94	97	94	92	95	93	91	90
4	104	99	94	91	102	97	94	91	95	92	90	94	91	89	92	90	88	87
5	101	95	91	87	99	94	90	87	92	89	86	91	88	86	89	87	85	84
6	98	91	87	84	96	91	87	84	89	86	83	88	85	83	87	84	82	81
7	95	88	84	81	94	87	83	81	86	83	80	85	82	80	84	82	79	78
8	92	85	81	78	91	85	81	78	84	80	78	83	80	77	82	79	77	76
9	89	82	78	75	88	82	78	75	81	78	75	80	77	75	80	77	75	74
10	87	80	76	73	86	79	76	73	79	75	73	78	75	72	78	75	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	390537
5°	385281
10°	318106
15°	256466
20°	165967
25°	40516
30°	9728
35°	2439
40°	773
45°	174
50°	96
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170653

CATALOG NUMBER: LDA4A09827D010TE LAR35FL 4LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.6	26.8
10°-20°	538.7	52.4
20°-30°	199.3	19.4
30°-40°	14.0	1.4
40°-50°	1.2	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1013.6	98.5
0°-40°	1027.6	99.9
0°-60°	1028.9	100.0
0°-90°	1028.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1028.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3166	
5°	3112	276
15°	2008	539
25°	298	199
35°	16	14
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170653

CATALOG NUMBER: LDA4A09827D010TE LAR35FL 4LFC1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3166.2
1°	3147.6
2°	3137.6
3°	3157.1
4°	3161.9
5°	3111.7
6°	3022.4
7°	2897.7
8°	2771.5
9°	2646.8
10°	2539.8
11°	2424.6
12°	2322.8
13°	2221.5
14°	2118.8
15°	2008.4
17.5°	1677.7
20°	1264.4
22.5°	782.2
25°	297.7
27.5°	122.3
30°	68.3
32.5°	32.5
35°	16.2
37.5°	8.6
40°	4.8
42.5°	2.4
45°	1.0
47.5°	0.5
50°	0.5
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P170653

CATALOG NUMBER: LDA4A09827D010TE LAR35FL 4LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)