

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170430

Luminaire Tested: **LDA4A09830D010TE LAR25NF 4LA1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P170430  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25629)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA4A09830D010TE LAR25NF 4LA1  
Description: PORTFOLIO 4" Adjustable Reflector, Self-flange Trim Ring, 25° Narrow Flood Optic, at 0° tilt  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 896.0 lumens  
Efficiency: N/A  
Efficacy: 64.7 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.45  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.84  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P170430  
CATALOG NUMBER: LDA4A09830D010TE LAR25NF 4LA1

### Luminous Intensity Polar Plot





TEST NUMBER: P170430

CATALOG NUMBER: LDA4A09830D010TE LAR25NF 4LA1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97	97	97	97																
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	95	94	94	94	94																
3	108	104	100	97	106	102	99	97	100	97	95	98	96	94	96	94	92	91	91	91	91																
4	105	100	96	93	103	99	95	93	97	94	92	95	93	91	93	91	90	88	88	88	88																
5	102	96	92	89	101	95	92	89	94	91	88	92	90	88	91	89	87	86	86	86	86																
6	99	93	89	86	98	93	89	86	91	88	85	90	87	85	89	86	84	83	83	83	83																
7	97	90	86	83	95	90	86	83	89	85	83	88	85	83	87	84	82	81	81	81	81																
8	94	88	84	81	93	87	83	81	86	83	81	85	82	80	85	82	80	79	79	79	79																
9	92	85	81	79	91	85	81	79	84	81	78	83	80	78	83	80	78	77	77	77	77																
10	89	83	79	76	89	83	79	76	82	79	76	81	78	76	81	78	76	75	75	75	75																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	499278
5°	437655
10°	326435
15°	207648
20°	110115
25°	24851
30°	5968
35°	1717
40°	580
45°	174
50°	96
55°	108
60°	123
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170430

CATALOG NUMBER: LDA4A09830D010TE LAR25NF 4LA1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	309.2	34.5
10°-20°	444.3	49.6
20°-30°	131.4	14.7
30°-40°	9.3	1.0
40°-50°	1.1	0.1
50°-60°	0.4	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	884.8	98.8
0°-40°	894.2	99.8
0°-60°	895.7	100.0
0°-90°	896.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	896.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4048	
5°	3535	309
15°	1626	444
25°	183	131
35°	11	9
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170430

CATALOG NUMBER: LDA4A09830D010TE LAR25NF 4LA1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4047.8
2.5°	3835.2
5°	3534.7
7.5°	3144.2
10°	2606.3
12.5°	2100.4
15°	1626.1
17.5°	1185.0
20°	838.9
22.5°	531.2
25°	182.6
27.5°	79.7
30°	41.9
32.5°	21.2
35°	11.4
37.5°	6.7
40°	3.6
42.5°	2.1
45°	1.0
47.5°	0.5
50°	0.5
52.5°	0.5
55°	0.5
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.0
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)