

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170562

Luminaire Tested: **LDA4A09930D010TE LAR35FL 4LAL1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170562
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26146)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A09930D010TE LAR35FL 4LAL1
Description: PORTFOLIO 4" Lensed Adjustable, Self-flange Trim Ring, 35° Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 863.9 lumens
Efficiency: N/A
Efficacy: 62.4 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.55
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13.84
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170562
CATALOG NUMBER: LDA4A09930D010TE LAR35FL 4LAL1

Luminous Intensity Polar Plot





TEST NUMBER: P170562

CATALOG NUMBER: LDA4A09930D010TE LAR35FL 4LAL1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96				96															
2	111	107	104	102	109	106	103	100	102	100	98	100	98	96	97	96	94				93																
3	107	103	99	96	106	101	98	95	99	96	94	96	94	92	94	92	91				90																
4	104	98	94	91	102	97	93	91	95	92	90	93	91	89	92	89	88				86																
5	101	94	90	87	99	94	90	87	92	89	86	90	88	85	89	87	85				83																
6	97	91	87	84	96	90	86	83	89	85	83	88	85	82	86	84	82				81																
7	94	88	83	80	93	87	83	80	86	82	80	85	82	79	84	81	79				78																
8	92	85	80	77	91	84	80	77	83	80	77	82	79	77	82	79	76				75																
9	89	82	78	75	88	82	77	75	81	77	75	80	77	74	79	76	74				73																
10	86	79	75	72	86	79	75	72	78	75	72	78	74	72	77	74	72				71																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	340039
5°	311696
10°	262884
15°	213164
20°	138048
25°	39795
30°	8702
35°	2469
40°	934
45°	384
50°	173
55°	86
60°	99
65°	117
70°	144
75°	0
80°	0
85°	0



TEST NUMBER: P170562

CATALOG NUMBER: LDA4A09930D010TE LAR35FL 4LAL1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.8	26.3
10°-20°	447.9	51.8
20°-30°	172.5	20.0
30°-40°	13.7	1.6
40°-50°	2.0	0.2
50°-60°	0.4	0.0
60°-70°	0.4	0.0
70°-80°	0.2	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	847.2	98.1
0°-40°	860.9	99.6
0°-60°	863.3	99.9
0°-90°	864.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	863.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2757	
5°	2517	227
15°	1669	448
25°	292	173
35°	16	14
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170562

CATALOG NUMBER: LDA4A09930D010TE LAR35FL 4LAL1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2756.8
1°	2734.7
2°	2712.1
3°	2659.0
4°	2589.1
5°	2517.4
6°	2438.7
7°	2362.1
8°	2277.6
9°	2186.1
10°	2098.9
11°	2015.7
12°	1929.0
13°	1846.3
14°	1761.8
15°	1669.3
17.5°	1397.6
20°	1051.7
22.5°	649.9
25°	292.4
27.5°	112.4
30°	61.1
32.5°	31.4
35°	16.4
37.5°	9.7
40°	5.8
42.5°	3.5
45°	2.2
47.5°	1.3
50°	0.9
52.5°	0.4
55°	0.4
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.4
80°	0.0
82.5°	0.0



TEST NUMBER: P170562

CATALOG NUMBER: LDA4A09930D010TE LAR35FL 4LAL1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.4



(END OF REPORT)