

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210772

Luminaire Tested: **LE_4B10D010 EC4B10209027 4LBW1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210772
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35168)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209027 4LBW1WH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 886.8 lumens
Efficiency: N/A
Efficacy: 64.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 13.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210772

CATALOG NUMBER: LE_4B10D010 EC4B10209027 4LBW1WH

Luminous Intensity Polar Plot





TEST NUMBER: P210772

CATALOG NUMBER: LE_4B10D010 EC4B10209027 4LBW1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	64	60		69	64	60		67
7	78	67	60	56	76	67	60	55	65	59	55		64	59	55		63
8	73	62	56	51	72	62	55	51	61	55	51		60	54	50		59
9	69	58	51	47	68	58	51	47	57	51	47		56	50	47		55
10	65	54	48	43	64	54	48	43	53	47	43		52	47	43		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60585
5°	61321
10°	63317
15°	66523
20°	68520
25°	67547
30°	62930
35°	53380
40°	40535
45°	25279
50°	12035
55°	4648
60°	2273
65°	1499
70°	1118
75°	971
80°	755
85°	0



TEST NUMBER: P210772

CATALOG NUMBER: LE_4B10D010 EC4B10209027 4LBW1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	6.1
10°-20°	166.2	18.7
20°-30°	255.7	28.8
30°-40°	246.7	27.8
40°-50°	128.6	14.5
50°-60°	27.1	3.1
60°-70°	6.3	0.7
70°-80°	2.5	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	475.6	53.6
0°-40°	722.3	81.4
0°-60°	878.0	99.0
0°-90°	886.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	886.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	554	
5°	559	54
15°	588	166
25°	560	256
35°	400	247
45°	164	129
55°	24	27
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P210772

CATALOG NUMBER: LE_4B10D010 EC4B10209027 4LBW1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	554.5
2.5°	555.6
5°	559.1
7.5°	563.8
10°	570.7
12.5°	580.0
15°	588.1
17.5°	592.8
20°	589.3
22.5°	582.3
25°	560.3
27.5°	533.6
30°	498.8
32.5°	452.4
35°	400.2
37.5°	343.4
40°	284.2
42.5°	225.0
45°	163.6
47.5°	110.2
50°	70.8
52.5°	42.9
55°	24.4
57.5°	15.1
60°	10.4
62.5°	8.1
65°	5.8
67.5°	4.6
70°	3.5
72.5°	3.5
75°	2.3
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)