

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210774

Luminaire Tested: **LE_4B10D010 EC4B10209727 4LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210774
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209727 4LBCS1MMS
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 784.1 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210774

CATALOG NUMBER: LE_4B10D010 EC4B10209727 4LBCS1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P210774

CATALOG NUMBER: LE_4B10D010 EC4B10209727 4LBCS1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	103	100	108	105	101	98	100	98	95		97	94	92		93
2	102	95	89	84	100	93	88	83	90	85	81		86	83	79		84
3	94	85	77	72	92	83	76	71	80	74	70		77	73	69		75
4	87	76	68	62	84	74	67	61	72	66	61		70	64	60		68
5	80	68	60	54	78	67	59	54	65	58	53		63	57	53		61
6	74	62	54	48	72	61	53	47	59	52	47		58	51	47		56
7	69	56	48	42	67	56	48	42	54	47	42		53	46	42		51
8	64	52	44	38	63	51	43	38	50	43	38		48	42	38		47
9	60	48	40	35	59	47	40	34	46	39	34		45	39	34		44
10	57	44	36	31	55	43	36	31	43	36	31		42	35	31		41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210774

CATALOG NUMBER: LE_4B10D010 EC4B10209727 4LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.9	4.3
10°-20°	95.2	12.1
20°-30°	139.1	17.7
30°-40°	159.1	20.3
40°-50°	152.9	19.5
50°-60°	118.0	15.1
60°-70°	65.9	8.4
70°-80°	19.2	2.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	268.2	34.2
0°-40°	427.3	54.5
0°-60°	698.2	89.1
0°-90°	784.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	784.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	360	
5°	357	34
15°	338	95
25°	302	139
35°	255	159
45°	199	153
55°	132	118
65°	66	66
75°	17	19
85°	0	1
90°	0	



TEST NUMBER: P210774

CATALOG NUMBER: LE_4B10D010 EC4B10209727 4LBCS1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	360.1
2.5°	360.1
5°	357.0
7.5°	355.5
10°	350.4
12.5°	344.4
15°	337.8
17.5°	331.2
20°	321.6
22.5°	313.9
25°	302.3
27.5°	290.6
30°	279.0
32.5°	267.3
35°	254.6
37.5°	242.0
40°	227.2
42.5°	214.0
45°	199.3
47.5°	182.6
50°	166.8
52.5°	149.6
55°	132.4
57.5°	114.6
60°	97.9
62.5°	81.2
65°	65.9
67.5°	51.7
70°	38.5
72.5°	26.9
75°	16.7
77.5°	8.6
80°	3.0
82.5°	1.0
85°	0.5
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)