

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170627

Luminaire Tested: **LDA4A09935D010TE LAR25NF 4LFC1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P170627  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26142)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA4A09935D010TE LAR25NF 4LFC1  
Description: PORTFOLIO 4" Flat Cone, Self-flange Trim Ring, 25° Narrow Flood Optic, at 0° tilt  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 922.8 lumens  
Efficiency: N/A  
Efficacy: 66.7 lumens/watt  
Spacing Criteria (0/90/45): 0.46 / 0.46 / 0.47  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.84  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P170627

CATALOG NUMBER: LDA4A09935D010TE LAR25NF 4LFC1

### Luminous Intensity Polar Plot





TEST NUMBER: P170627

CATALOG NUMBER: LDA4A09935D010TE LAR25NF 4LFC1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	104	103	102	101	100	99	99	97
2	111	108	105	103	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	104	100	97	106	102	99	96	100	97	95	98	95	94	95	94	92	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	88
5	102	96	92	89	100	95	92	89	94	91	88	92	89	87	91	89	87	86
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	83
7	96	90	86	83	95	89	86	83	88	85	83	87	84	82	86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	76
10	89	82	79	76	88	82	78	76	81	78	76	81	78	76	80	77	75	74

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	477718
5°	438708
10°	327713
15°	218285
20°	118241
25°	28213
30°	6609
35°	1882
40°	644
45°	227
50°	77
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170627

CATALOG NUMBER: LDA4A09935D010TE LAR25NF 4LFC1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	307.1	33.3
10°-20°	463.0	50.2
20°-30°	141.4	15.3
30°-40°	10.2	1.1
40°-50°	1.1	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	911.4	98.8
0°-40°	921.7	99.9
0°-60°	922.8	100.0
0°-90°	922.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	922.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3873	
5°	3543	307
15°	1709	463
25°	207	141
35°	12	10
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170627

CATALOG NUMBER: LDA4A09935D010TE LAR25NF 4LFC1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3873.0
1°	3829.3
2°	3766.5
3°	3719.2
4°	3659.1
5°	3543.2
6°	3397.4
7°	3215.1
8°	3027.0
9°	2826.4
10°	2616.5
11°	2416.3
12°	2233.1
13°	2057.5
14°	1888.1
15°	1709.4
17.5°	1284.2
20°	900.8
22.5°	562.1
25°	207.3
27.5°	83.8
30°	46.4
32.5°	23.2
35°	12.5
37.5°	7.1
40°	4.0
42.5°	2.2
45°	1.3
47.5°	0.4
50°	0.4
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P170627

CATALOG NUMBER: LDA4A09935D010TE LAR25NF 4LFC1

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)