

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210817

Luminaire Tested: **LE_4B10D010 EC4B10208030 4LBPS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210817
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10208030 4LBPS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1328.0 lumens
Efficiency: N/A
Efficacy: 134.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210817

CATALOG NUMBER: LE_4B10D010 EC4B10208030 4LBPS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P210817

CATALOG NUMBER: LE_4B10D010 EC4B10208030 4LBPS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	107	104	100	97	99	97	94		96	93	91		92
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73
4	85	74	66	59	83	72	65	59	70	63	58		68	62	57		66
5	78	66	58	51	76	65	57	51	63	56	51		61	55	50		59
6	73	60	51	45	71	59	51	45	57	50	44		55	49	44		54
7	67	54	46	40	66	54	46	40	52	45	40		51	44	39		49
8	63	50	41	36	61	49	41	36	48	41	35		46	40	35		45
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42
10	55	42	34	29	54	42	34	29	41	34	29		40	33	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210817

CATALOG NUMBER: LE_4B10D010 EC4B10208030 4LBPS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.7	3.8
10°-20°	144.5	10.9
20°-30°	217.6	16.4
30°-40°	259.0	19.5
40°-50°	258.5	19.5
50°-60°	210.2	15.8
60°-70°	129.3	9.7
70°-80°	50.1	3.8
80°-90°	8.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	412.8	31.1
0°-40°	671.8	50.6
0°-60°	1140.5	85.9
0°-90°	1328.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1328.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	535	
5°	534	51
15°	513	145
25°	474	218
35°	415	259
45°	336	258
55°	235	210
65°	130	129
75°	46	50
85°	6	8
90°	0	



TEST NUMBER: P210817

CATALOG NUMBER: LE_4B10D010 EC4B10208030 4LBPS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	535.1
2.5°	535.8
5°	533.5
7.5°	530.4
10°	526.4
12.5°	519.3
15°	513.1
17.5°	503.6
20°	493.3
22.5°	484.0
25°	473.6
27.5°	459.5
30°	445.3
32.5°	432.0
35°	414.7
37.5°	395.8
40°	378.5
42.5°	357.3
45°	335.9
47.5°	313.2
50°	288.7
52.5°	263.6
55°	235.2
57.5°	207.8
60°	181.0
62.5°	155.0
65°	129.8
67.5°	106.3
70°	84.2
72.5°	63.7
75°	45.6
77.5°	29.9
80°	18.1
82.5°	11.0
85°	6.3
87.5°	3.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)